

## 88777 Multi-Conductor - CMP Rated (Plenum) Cable

For more Information  
please call

1-800-Belden1



### Description:

22 AWG stranded (7x30) TC conductor, FEP insulation, twisted pairs individually shielded with Beldfoil® (100% coverage), overall jacket per table below, 22 AWG stranded TC drain wire.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
3	22	7x30	TC - Tinned Copper	0.762

#### Insulation

##### Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (mm)
Teflon®	FEP - Fluorinated Ethylene Propylene	1.27

#### Inner Shield

##### Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

##### Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 16x34

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

#### Outer Shield

##### Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Teflon®	FEP - Fluorinated Ethylene Propylene

### Overall Cabling

Overall Nominal Diameter: 5.944 mm

#### Pair

##### Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

##### Pair Lay Length & Direction:

Lay Length (mm)	Twists/ft. (twist/m)	Direction
38.09985	26.248	Left Hand Lay

### Mechanical Characteristics (Overall)

## 88777 Multi-Conductor - CMP Rated (Plenum) Cable

Operating Temperature Range:	-70°C To +200°C
Bulk Cable Weight:	57.891 Kg/Km
Max. Recommended Pulling Tension:	364.752 N
Min. Bend Radius (Install)/Minor Axis:	58.420 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

#### Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	8777

### Electrical Characteristics (Overall)

#### Nom. Characteristic Impedance:

Impedance (Ohm)

50

#### Nom. Inductance:

Inductance (µH/m)

0.59058

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

101.711

#### Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

219.827

#### Nominal Velocity of Propagation:

VP (%)

69

#### Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

52.496

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 37.075 Ohm/km

#### Max. Operating Voltage - UL:

Voltage

300 V RMS

#### Max. Recommended Current:

## 88777 Multi-Conductor - CMP Rated (Plenum) Cable

### Current

1.96 Amps per conductor @ 25°C

### Notes (Overall)

**Notes:** Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
88777 002100	30 MT	2.722 KG	RED	C	3 SH PR #22 FEP FEP
88777 0021000	305 MT	19.051 KG	RED	C	3 SH PR #22 FEP FEP
88777 002500	152 MT	8.618 KG	RED	C	3 SH PR #22 FEP FEP

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 04-17-2008

© 2011 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.