

# LED MONITOR

## E2260V

22" CLASS

21.5" diagonal

### HIGHLIGHTS

LED Backlighting

Ultra Slim Design

Full HD 1080p Resolution



### FEATURES

- LED Backlighting
- Ultra Slim Design
- Full HD 1080p Resolution
- 5M:1 Digital Contrast Ratio
- ENERGY STAR® Qualified
- Photo Effect
- HDMI™ Input
- FLATRON *f*-Engine



## Is it a monitor? Or something better?

The ultimate in LG Monitor displays is now available with the E60. Truly a marvel, it offers groundbreaking design elements, smart innovations like LED backlighting and the wonders of Full 1080p resolution.

Imagine anything you might want in a monitor display and it's been made a reality with the E60.



You won't believe your eyes. Tired of dark scenes or dull colors? LG's LED technology delivers amazing clarity and color detail as well as a more energy efficient monitor compared to conventional monitors.



The ultra slim width of less than 1" creates a uniquely sleek and delicate appearance that accentuates any decor.



This stunning picture is the reason you wanted HDTV in the first place. With almost double the pixel resolution, Full HD 1080p gives it superior picture quality over standard HDTV. You'll see details and colors like never before.

# LED MONITOR

## E2260V



### PANEL SPECIFICATION

Screen Size	22" Class (21.5" diagonal)
Panel Type	TN
Aspect Ratio	16:9
Resolution	1920 x 1080p
Brightness (cd/m2)	250
Contrast Ratio (DFC)	5,000,000:1
Response Time (GTG)	5ms (Typical)
Viewing Angle (H/V)	170°
Display Colors	16.7M
Panel Surface	Anti-Glare, 3H

### FREQUENCY

Analog	30-83kHz/56-75Hz
Digital	30-83kHz/56-75Hz

### CONNECTIVITY

D-Sub	1
DVI-D	1
HDMI™	1
Headphone Out	1

### FEATURES

Fun Package	
Photo Effect	•
4:3 in Wide	•
f-engine	•
sRGB	•
DDC/CI	•
HDCP	•
ARC	•
Auto Resolution	•
Plug & Play	DDC2B

### CABINET/STAND

Cabinet Color	Glossy Black
Base Detachable	•
Stand Tilt (Degrees)	5°-15°

### INCLUDED ACCESSORIES

15-pin D-Sub Signal Cable	•
Power Cord	•

### COMPLIANCE & STANDARDS

UL(cUL)	•
TUV-GS	TUV-Type
SEMKO	•
FCC-B, CE	•
EPA	•
Windows 7	•

### POWER

Voltage, Hz	100V ~ 240V, 56/75Hz
On Mode (Average)	26W (Max)
Standby Mode	<1W (Max)
Power Off	<0.5W (Max)
ENERGY STAR® Qualified	•

### DIMENSIONS & WEIGHT

Dimensions (with Stand)	20.03" x 15.44" x 6.72"
Dimensions (without Stand)	20.03" x 15.25" x 1.22"
Shipping Dimensions	22.87" x 17.75" x 5.86"
Weight (with Stand)	5.00 lbs
Weight (without Stand)	4.45 lbs
Shipping Weight	9.04 lbs

### WARRANTY/UPC

Limited Warranty	1 Year Parts & Labor
UPC	719192187344

[LG.com](http://LG.com)

LG Electronics U.S.A., Inc.

1000 Sylvan Avenue Englewood Cliffs, NJ 07632  
Customer Service and Technical Support: (800) 243-0000

Design, features and specifications are subject to change without notice. Non-metric weights and measurements are approximate. LCD monitor with LED backlighting.

© 2010 LG Electronics USA, Inc. All rights reserved. "LG Life's Good" is a registered trademark of LG Corp. All other product and brand names are trademarks or registered trademarks of their respective companies. 07/21/10