

DWFC Series Heat Shrink Tubing



Features:

- Excellent mechanical strength.
- Excellent abrasion resistance.
- Excellent optical clarity.
- Environmental sealing.
- Shrink ratio 4:1.



It is a flexible, heat-shrinkable, dual-wall tubing with an integrally bonded melt able adhesive inner liner designed to offer moisture proof encapsulation to a wide variety of substrates. Available in clear, DWFC offers excellent clarity for protection of substrates that may need to be inspected during service. The tough outer jacket gives excellent mechanical strength with a high resistance to splitting. The high shrinkage ratio means that only four sizes are needed to give protection to a full range of irregular shapes with widely varying dimensions.

Performance

Test	Test Method	Test Requirement
Minimum Inner Wall Adhesion DWFC to aluminium	-	60N/25mm
Heat Shock	4 Hours at 200°C	Pass-no Dripping, Cracking or Flowing of Outer Wall
Heat Ageing	168 Hours at 120°C	
Low Temperature Flexibility	4 Hours at -55°C	Pass-no Cracking
Fluid Resistance	24 Hours at 23°C, ISO 37	Minimum Tensile Strength : 15MPa Minimum Ultimate Elongation : 200%
	Test Fluids	Diesel Fuel (BS 2869 Class A1) Break Fluid (H-515) Lubricating Oil (0-149)

DWFC Series Heat Shrink Tubing



Specification Table


Inside Diameter		Wall Thickness		Length (m)	Part Number
Minimum Expanded as Supplied (D)	Maximum Recovered After Heating (d)	Nominal Total Wall Recovered After Heating (W)	Nominal Meltable Wall Recovered After Heating (W1)		
4.0	1.0	0.8	0.25	1.2	DWFC-4/1-X-STK
8.0	2.0	0.9			DWFC-8/2-X-STK
12.0	3.0	1.2	0.40		DWFC-12/3-X-STK

Dimensions : Millimetres (Unless Specified)

Note:

The wall thickness of the tubing will be less than specified if recovery is restricted during shrinkage.

Part Number Explanation:



Inside Diameter : Expanded as supplied/Recovered after heating.

Colour Code : X = Clear.

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. SPC pro-Power is the registered trademark of the Group. © Premier Farnell plc 2010.