## **Detailed Specifications & Technical Data**



#### 1673A Coax - 50 Ohm Microwave Cable

For more Information please call

1-800-Belden1



### **Description:**

RG-402/U type, 19 AWG solid .036" silver-plated copper-covered steel conductor, TFE Teflon® insulation, copper-tin composite shield (100% coverage), unjacketed.

nysical Characteristics (Overall)	
Conductor AWG:	
# Coax AWG Stranding Conductor Material	Dia. (mm)
1 19 Solid SPCCS - Silver Plated Coppe	er Covered Steel 0.9144
nsulation	
Insulation Material:	
Insulation Trade Name Insulation Material Dia   Teflon® TFE - Tetrafluoroethylene 2.9	a. (mm) 9464
Outer Shield Outer Shield Material:	
Layer # Type Outer Shield Material Coverage (%)	
1 Tape Copper Foil 100   2 Braid Tin-Filled Composite 100	
Overall Cabling	2.505 mm
Overall Nominal Diameter:	3.505 mm
echanical Characteristics (Overall)	
Operating Temperature Range:	-70°C To +200°C
UL Temperature Rating:	105°C
Non-UL Temperature Rating:	200°C
Bulk Cable Weight:	29.764 Kg/Km
Max. Recommended Pulling Tension:	311.374 N
Min. Bend Radius (Install)/Minor Axis:	6.350 mm
Min. Bend Radius (Continuous Flexing):	19.050 mm
oplicable Specifications and Agency Co	ompliance (Overall)
pplicable Standards & Environmental Progr	
AWM Specification:	UL Style 10245
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes

# **Detailed Specifications & Technical Data**

#### METRIC MEASUREMENT VERSION

3000

86.9465



#### 1673A Coax - 50 Ohm Microwave Cable

М	MII Order #39 (China RoHS):				Yes
R	G Type:	:			402/U
Flame Test					
		me Test:			Horizontal Wire
Suita					
	-	y - Indoor:			Yes
		-			
		y - Outdoor:			Yes
		n-Plenum			
P	lenum (	Y/N):			No
Electr	rical C	haracteris	tics (Ove	erall)	
		teristic Imped		,	
	pedance (				
50					
Nom.	Inducta	nce:			
Ind	uctance	(µH/m)			
0.22	2967				
Nom.	Capacit	ance Conduc	tor to Shie	eld:	
Cap	<b>pacitance</b> 7895				
		city of Propa	action		
VP		city of Propa	yanon.		
69.5					
Nomir	nal Dela	v			
	lay (ns/m				
	9026	,			
Nom	Conduc	⊐ ctor DC Resis	tance:		
		C (Ohm/km)	anoor		
	2605	(- /			
Nomir	nal Oute	er Shield DC I	Resistance	:	
		C (Ohm/km)			
	7645				
Maxin	num VS	WR:			
Des	scription		Freq. (MHz)	Max. VSWR	e
Rar	mp Functi	on, End Points		1.1	
			20000	1.3	
Nom.	Attenua	tion:			
		Attenuation (d	B/100m)		
500		26.248			
100 200		39.372 59.3861			
300		75.1349			
500		101.711			
700	00	124.022			
100		152.895			
150		193.907			
180		215.89			
200		229.67			
	Attenua				
		Attenuation (d	B/100m)		
500		31.1695			
100	JU	47.5745			

## **Detailed Specifications & Technical Data**



#### METRIC MEASUREMENT VERSION

#### 1673A Coax - 50 Ohm Microwave Cable

5000	118.116
10000	177.174
20000	275.604

#### Nom. Power Rating:

Freq. (MHz)	Rating (W)
500	600
1000	401
2000	268
3000	211
5000	157
7000	129
10000	105
15000	83
18000	74
20000	70

#### Max. Operating Voltage - UL:



Max. Operating Voltage - Non-UL:

Voltage 1900 V RMS

#### **Misc. Information (Overall)**

#### **Notes (Overall)**

Notes: US Patents 4, 694, 122 & 5, 293, 001. Patent held in the U.S., Singapore, Australia, Germany, France, and England. Patent pending in Japan. Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

#### **Related Documents:**

No related documents are available for this product

#### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1673A TIN100	30 MT	1.406 KG	TIN - COLOR	С	#19 TFE BRD TINNED COAX
1673A TIN250	76 MT	3.289 KG	TIN - COLOR	CV	#19 TFE BRD TINNED COAX
1673A TIN50	15 MT	0.816 KG	TIN - COLOR		#19 TFE BRD TINNED COAX
1673A TIN500	152 MT	6.350 KG	TIN - COLOR		#19 TFE BRD TINNED COAX

#### Notes:

C = CRATE REFL PUT-UP

V = 250' PUT-UP EXACT LENGTH MAXIMUM OF 3 PIECESMINIMUM LENGTH 50'500' PUT-UP EXACT LENGTH MAXIMUM OF 5 PIECESMINIMUM LENGTH 50'

**Revision Number: 2** Revision Date: 09-30-2009

© 2011 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this products are subject to believe standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.



METRIC MEASUREMENT VERSION

1673A Coax - 50 Ohm Microwave Cable