

FUME EXTRACTION



ARM-EVAC 200

Arm-Evac 200 - Versatile Performance for 1 to 4 Workstations

Features

High volume air flow Heavy duty brushless motor 18 gauge steel construction On/off switch located on front panel Easy filter access Compact and self-contained Includes pre-filter, general purpose combo filter and power cord

Specifications

Unit:	Arm-Evac 200
Power Requirements:	120VAC, 60Hz 3 Amps 230VAC, 50Hz 1.38 Amps
Size:	280mm (11")W x 330mm (13")D x 395mm (15.5")H
Weight:	14 Kg (32 lbs.)
Sound Level:	59 dBA @ 2m (6')
# Inlets:	Two 75mm (3") dia.
Free Blowing Flow Rate:	510 m3/h (300 cfm)
# Workbench Connections:	45mm (1.75") and 50mm (2") 4 65mm (2.5") and 75mm (3") 2
Microprocessor Controls:	No
Maximum Duct Run:	5m (16') per inlet 324mm (12.75")H

Silencer/Mobile Cart for Arm-Evac 200/250



P/N 8885-1225

Constructed of 18-gauge steel and acoustical foam baffle liner. Includes front locking casters. Dimensions: 280mm (11")W x 330mm (13")D x 150mm (6")H
Weight: 4.5 Kg (10lbs)