

For more Information  
please call

1-800-Belden1



## Description:

Low noise, RG-174/U Type, 26 AWG stranded (7x34) .019" bare copper-covered steel conductor, polyethylene insulation, conductive layer, TC braid shield (90% coverage), PVC jacket.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	26	7x34	BCCS - Bare Copper Covered Steel	0.4826

### Insulation

Insulation Material:

Layer #	Insulation Material	Dia. (mm)
1	PE - Polyethylene	1.1176
2	Conductive PVC - Polyvinyl Chloride	1.4224

### Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	90

### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

### Overall Cabling

Overall Nominal Diameter: 2.565 mm

## Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +60°C

Non-UL Temperature Rating: 60°C

Bulk Cable Weight: 10.417 Kg/Km

Max. Recommended Pulling Tension: 64.054 N

Min. Bend Radius (Install)/Minor Axis: 25.400 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

Mil Order #39 (China RoHS): Yes  
 RG Type: 174/U

**Plenum/Non-Plenum**

Plenum (Y/N): No

**Electrical Characteristics (Overall)**

**Nom. Characteristic Impedance:**

Impedance (Ohm)  
 50

**Nom. Capacitance Conductor to Shield:**

Capacitance (pF/m)  
 124.678

**Nominal Velocity of Propagation:**

VP (%)  
 62

**Nom. Conductor DC Resistance:**

DCR @ 20°C (Ohm/km)  
 318.257

**Nominal Outer Shield DC Resistance:**

DCR @ 20°C (Ohm/km)  
 45.934

Other Electrical Characteristic 1: NBS Low Noise Test (Modified), MIL-C-17 Paragraph 4.8.14, 8 mV Peak to Peak Max

Max. Noise Level (Peak to Peak): 5 mV

**Notes (Overall)**

Notes: Not recommended for RF use.

**Related Documents:**

No related documents are available for this product

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9239 010100	30 MT	0.454 KG	BLACK		#26AWG LOW NOISE COAX
9239 0101000	305 MT	3.629 KG	BLACK		#26 AWG LOW NOISE COAX
9239 010500	152 MT	2.041 KG	BLACK		#26AWG LOW NOISE COAX

Revision Number: 1    Revision Date: 05-14-2007

© 2011 Belden, Inc  
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.