

EVERBUILD P14 CONCENTRATED CENTRAL HEATING SYSTEM INHIBITOR

Colour	Product Code	Pack Size	Box Qty
-	P14INHIBC3	310ml	12

Product Description

EVERBUILD P14 SYSTEM INHIBITOR CONCENTRATE is a multi-purpose treatment, specifically designed to protect the entire central heating system from scale, sludge and corrosion.

Benefits

- WRAS Approved formulation.
- Buildcert Performance Standard
- Compatible with all EVERBUILD central heating products.
- Does not contain mineral oil.
- compatible with plastic and fiberglass header tanks and with all metals used in central heating systems which includes iron, copper, steel, brass and aluminium.
- Suitable for microbore systems constructed from plastic pipes

Areas for Use

- New and existing central heating systems.
- Extensions to existing systems.

Limitations

- Use only as directed.
- Only suitable for fully indirect systems.
- Not suitable for use in PRIMATIC single feed cylinders.
- Central heating systems should be protected with P14 SYSTEM INHIBITOR.

Application

For use in accordance with BS7593:2006. Unless completing annual top up, for best results, pre-treat the system with P11 SYSTEM CLEANSER prior to adding P14.

- 1) Locate a convenient radiator with an accessible bleed screw- preferably in a bathroom or kitchen which has no carpets.
- 2) Close both valves.
- 3) Remove the bleed screw using a radiator key. (Have a cloth ready to absorb spillage)
- 4) Cut the tip of the cartridge taking care not to damage the thread. Attach the injector nozzle and apply using a standard sealant gun.
- 5) Open one radiator valve and inject the entire contents of the tube.
- 6) Close the radiator valve, remove the injector nozzle and replace the bleed screw.

- 7) Return the valves to their original position.
- 8) Bleed radiator to remove any trapped air.

If boiler suffers from knocking and kettling, use in conjunction with P12 NOISE SILENCER for optimum long term protection.

Health & Safety

Consult COSHH data sheet for full list of hazards.

Storage

Store in original container away from frost in a dry area.

Coverage

Minimum dosage to achieve Buildcert performance standard: 310ml per 70ltr system capacity.

Shelf Life

36 months in original unopened containers.

The technical data contained herein is based on our present knowledge and experience and we cannot be held liable for any errors, inaccuracies, omissions or editorial failings that result from technological changes or research between the date of issue of this document and the date the product is acquired. Before using the product, the user should carry out any necessary tests in order to ensure that the product is suitable for the intended application. Moreover, all users should contact the seller or the manufacturer of the product for additional technical information concerning its use if they think that the information in their possession needs to be clarified in any way, whether for normal use or a specific application of our product. Our guarantee applies within the context of the statutory regulations and provisions in force, current professional standards and in accordance with the stipulations set out in our general sales conditions. The information detailed in the present technical data sheet is given by way of indication and is not exhaustive. The same applies to any information provided verbally by telephone to any prospective or existing customer.