


LUMBERJACK TRIPLE ACTION WOOD TREATMENT



Colour	Product Code	Pack Size	Box Qty
Clear	LJUN01	1Ltr	10
	LJUN02	2.5Ltr	6
	LJUN05	5Ltr	4
	LJUN25	25Ltr	1

Product Description

LUMBERJACK TRIPLE ACTION WOOD TREATMENT takes care of all your wood treatment and preservation needs in the one can. It is a low solvent; low odour solution based on Micro-fine active technology with added fungicides, algacides and Permethrin to actively kill and protect against all known wood rot; decay, fungi and wood boring insects. The fungicides and algacides present in these formulations are finely dispersed so that wood penetration and hence effectiveness is much greater than standard wood preservation products

LUMBERJACK TRIPLE ACTION WOOD TREATMENT is fast drying and non flammable and application to wet timbers is possible without loss of performance. It is specifically designed to deeply penetrate all wood and joinery to give long lasting protection from damage caused by wet rot, dry rot, decay; fungi and wood boring insects/larvae.

Benefits

- Solvent Free formula
- Non Flammable.
- Internal and external use.
- Can be applied to damp timbers..

Areas For Use

For interior and exterior use on wood such as:

- Sheds and Garages
- Fencing and Farm Buildings
- Roof beams and joists
- Garden Furniture.
- Floorboards
- Window frames and doors

Limitations

- Ready to use - do not dilute.
- For use only as specified as a surface biocide.
- Always use coarse rather than fine mist generators.
- Do not apply to surfaces on which food is prepared.
- Avoid contact with bitumen, roofing felt or plastics.

- It is the user's responsibility to determine suitability for use. If in doubt, contact Technical Services Department for advice.

Surface Preparation

Ensure that surfaces are clean, and free from paint varnish, stain, grease, bark or any other contaminants. Surfaces may be damp. If decay is already present, remove all decayed wood and replace with sound treated timber.

Precautionary Notes

ALWAYS READ STATUTORY CONDITIONS RELATING TO USE BEFORE STARTING ANY WORK. Ensure good ventilation before applying and after application until the treatment has dried (HSE statutory 1 hour re-entry time or until surfaces are dry) NOTE: drying times will be extended in cold weather and if ventilation is restricted. Avoid contact with skin and eyes, Remove any splashes immediately. Clean up spills immediately (to avoid staining) with warm soapy water.

In roof areas, felt under tiles must be protected from contact with the fluid. Roof insulation's must be removed and only replaced when treated timbers are thoroughly dry. Water storage tanks must be covered.

When treating flooring and joists, boards should be left up for as long as possible to assist ventilation/drying.

Switch off electrical circuits in the area being treated before and for 48 hours after treatment. PVC covered electrical wiring will not normally be affected, but we recommend wiping any excess from cables wherever possible.

Application

Shake well before use. Apply by brush, spray or dipping. Apply a minimum of two coats if brushing or spraying. The second coat should be applied after the first coat has soaked in but before it is dry. Pay particular attention to thoroughly soaking the end grain. Where possible, dip the end grains of the timber for maximum protection.

Coverage Guide

Joinery, floorboards, furniture roof joists etc: Apply 1 litre of product per 3 - 4m² of surface.

Ideally this should be applied as 2-3 even coats leaving at least 2 hours between applications or dip for three minutes.

Timber not in ground contact: 3 coats by brush or spray or dip for 10 minutes. Coverage: 4m² per litre.

Timber in ground contact: Soak for 1 hour. Coverage: 40 litres per cubic meter.

Health & Safety

LUMBERJACK TRIPLE ACTION WOOD TREATMENT

UN 3082

Contains: Permethrin; Propiconazole

Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment..

Keep out of the reach of children

In case of contact with eyes, rinse immediately with plenty of water and seek medical advice

After contact with skin, wash immediately with plenty of soap and water.

Wear suitable protective clothing, gloves and eye / face protection.

In case of accident or if you feel unwell, seek medical advice immediately (show label where possible)

Avoid release to the environment. Refer to special instructions / safety data sheets

Contains : Propiconazole 0.45%(w/w): Permethrin 0.1%(w/w)

STATUTORY CONDITIONS RELATION TO USE :

To avoid risk to man and the environment comply with the instructions for use.

FOR USE ONLY AS A WOOD PRESERVATIVE.

Wear suitable protective clothing and eye / face protection. Take off immediately all contaminated clothing. Do not breathe spray mist. Otherwise wear respiratory protective equipment and eye protection (see HSE Guidance Booklet HSE (G) 53: "The Selection, Use and maintenance of Respiratory Protective Equipment - A practical guide"). COVER ALL WATER STORAGE TANKS before application. REMOVE OR COVER ALL FISH TANKS AND BOWLS before application. DO NOT CONTAMINATE FOODSTUFFS, EATING UTENSILS OR FOOD CONTACT SURFACES other than outdoor tables. EXCLUDE ALL UNPROTECTED PERSONS AND ANIMALS DURING TREATMENT AND FOR AT LEAST 1 HOUR AFTER TREATMENT IS COMPLETED. ENSURE THERE IS A PHYSICAL BARRIER TO PREVENT CONTACT BY UNPROTECTED PERSONS AND ANIMALS UNTIL THE TREATED SURFACES ARE VISIBLY DRY. ALL BATS ARE PROTECTED UNDER THE WILDLIFE AND COUNTRYSIDE ACT 1981. BEFORE TREATING ANY STRUCTURES USED BY BATS, CONSULT ENGLISH NATURE, SCOTTISH NATURAL HERITAGE OR THE COUNTRYSIDE COUNCIL FOR WALES. DO NOT USE ON BEEHIVES OR BEE KEEPING EQUIPMENT. This material and its container must be disposed of in a safe way. Do not empty into drains. Avoid contact with eyes. Avoid contact with skin. In case of contact with eyes, rinse immediately with plenty of water and seek medical advice. Do not contaminate ground, waterbodies or water courses with chemicals or used container. This product is approved under The Control of Pesticide Regulations (1986) for use as directed. HSE 8529.

PRECAUTIONS :

Harmful to aquatic organisms. May cause long term adverse effects in the aquatic environment. Keep out of the reach of children. Keep only in the original container. KEEP IN A SAFE PLACE. Keep away from food, drink and animal feeding stuffs. WASH ANY CONTAMINATION from eyes and skin immediately. WASH HANDS AND EXPOSED SKIN before meals and after use. In case of accident or if you feel unwell seek medical advice immediately (show label where possible). Use within 2 years of manufacture. PROTECT FROM FROST. Use only in accordance with the directions on the label.

Storage

Store at moderate temperatures in original containers away from children.

Shelf Life

Use within 2 years of manufacture.

The technical data contained herein is based on our present knowledge and experience and we cannot be held liable for any errors, inaccuracies, omissions or editorial failings that result from technological changes or research between the date of issue of this document and the date the product is acquired. Before using the product, the user should carry out any necessary tests in order to ensure that the product is suitable for the intended application. Moreover, all users should contact the seller or the manufacturer of the product for additional technical information concerning its use if they think that the information in their possession needs to be clarified in any way, whether for normal use or a specific application of our product. Our guarantee applies within the context of the statutory regulations and provisions in force, current professional standards and in accordance with the stipulations set out in our general sales conditions. The information detailed in the present technical data sheet is given by way of indication and is not exhaustive. The same applies to any information provided verbally by telephone to any prospective or existing customer.