

5400FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled



For more Information
please call

1-800-Belden1



Description:

20 AWG bare copper conductors, PP insulation, conductors cabled, Beldfoil® shield tape (foil side out) with drain wire, PVC jacket with ripcord, sequential footage marking every two feet.

Usage (Overall)

Suitable Applications: Intercom/PA Systems, Sound/Audio Systems

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	20	7x28	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PP - Polypropylene	0.178

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.432

Outer Jacket Ripcord: Yes

Overall Cabling

Overall Cabling Lay Length & Direction:

Length (mm)	Twists (m.)
76.1997	1.2192

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Red

Overall Nominal Diameter: 3.505 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 23.216 Kg/Km

Max. Recommended Pulling Tension: 165.028 N

5400FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Min. Bend Radius (Install)/Minor Axis:	34.925 mm
--	-----------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR
NEC Articles:	800
CEC/C(UL) Specification:	CMG
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Vertical Shaft
C(UL) Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6400FE

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance ($\mu\text{H}/\text{m}$)
0.509

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
142.724

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
257.559

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
33.7943

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
54.793

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
3.75 Amps per conductor @ 25°C (10°C rise in temp)

Related Documents:

No related documents are available for this product

5400FE Multi-Conductor - Commercial Audio Systems - 2 Conductors Cabled

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5400FE 008U1000	305 MT	6.804 KG	GRAY		2 #20 PP FS FRPVC
5400FE 008U500	152 MT	3.402 KG	GRAY		2 #20 PP FS FRPVC
5400FE 0081000	305 MT	6.350 KG	GRAY	C	2 #20 PP FS FRPVC
5400FE 008500	152 MT	3.402 KG	GRAY		2 #20 PP FS FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 06-03-2008

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.