

8424 Multi-Conductor - Four-Conductor Star Quad, Low-Impedance Cable



For more Information
please call

1-800-Belden1

**Description:**

20 AWG stranded (26x34) high-conductivity tinned copper conductors, EPDM rubber insulation, rayon braid, TC braid shield (85% coverage), cotton wrap, EPDM rubber jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (mm)
4	20	26x34	High Conductivity TC - Tinned Copper	0.9398

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
EPDM - Ethylene Propylene Diene Monomer Rubber	0.5842	2.1082

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	85

Outer Shield Separator Material: Cotton Wrap

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
EPDM - Ethylene Propylene Diene Monomer Rubber	0.9144

Overall Cabling

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green

Overall Cabling Separator Material: Rayon Braid

Overall Nominal Diameter: 7.468 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -50°C To +90°C

Non-UL Temperature Rating: 60°C

Bulk Cable Weight: 90.780 Kg/Km

Max. Recommended Pulling Tension: 386.993 N

Min. Bend Radius (Install)/Minor Axis: 74.930 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU CE Mark: Yes

8424 Multi-Conductor - Four-Conductor Star Quad, Low-Impedance Cable

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

52

Nom. Inductance:

Inductance (μH/m)

0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

154.207

Nom. Cap. Between Cond. in a Quad Config.:

Capacitance (pF/m)

193.579

Nominal Velocity of Propagation:

VP (%)

52

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

33.4662

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

10.4992

Max. Operating Voltage - UL:

Voltage

600 V RMS

Max. Recommended Current:

Current

3.2 Amps per conductor @ 25°C

Other Electrical Characteristic 1: 2/c 17AWG equivalent DCR when connected to a 3-pin XLR

Notes (Overall)

Notes: Quad connection scheme: The black and red wires (or wires directly opposite one another) are connected together to form one conductor, and similarly the white and green wires (or remaining wires) are connected together to form the second conductor.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8424 010U500	152 MT	14.515 KG	BLACK		4 #20 EPDM SHLD EPDM

METRIC MEASUREMENT VERSION

8424 Multi-Conductor - Four-Conductor Star Quad, Low-Impedance Cable

8424 010100	30 MT	3.084 KG	BLACK		4 #20 EPDM SHLD EPDM
8424 0101000	305 MT	29.030 KG	BLACK	C	4 #20 EPDM BRD EPDM
8424 010250	76 MT	6.917 KG	BLACK	C	4 #20 EPDM BRD EPDM
8424 010500	152 MT	13.835 KG	BLACK	C	4 #20 EPDM BRD EPDM

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.