

8723 Multi-Conductor - Shielded Twisted Pair Cable

For more Information
please call

1-800-Belden1



Description:

22 AWG stranded (7x30) tinned copper conductors, polypropylene insulation, twisted pairs, individually Beldfoil® shielded (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

| # Pairs | AWG | Stranding | Conductor Material |
|---------|-----|-----------|--------------------|
| 2 | 22 | 7x30 | TC - Tinned Copper |

Insulation

Insulation Material:

| Insulation Material |
|---------------------|
| PP - Polypropylene |

Inner Shield

Inner Shield Material:

| Inner Shield Trade Name | Type | Inner Shield Material | Coverage (%) |
|-------------------------|------|------------------------------|--------------|
| Beldfoil® (Z-Fold®) | Tape | Aluminum Foil-Polyester Tape | 100 |

Inner Shield Drain Wire AWG:

| AWG |
|-----|
| 24 |

Inner Shield Drain Wire Stranding: 7x32

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Shield

Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded |

Outer Jacket

Outer Jacket Material:

| Outer Jacket Material |
|--------------------------|
| PVC - Polyvinyl Chloride |

Overall Cabling

Overall Nominal Diameter: 4.064 mm

Pair

Pair Color Code Chart:

| Number | Color |
|--------|---------------|
| 1 | Red & Black |
| 2 | Green & White |

Pair Lay Length & Direction:

| Lay Length (mm) | Twists/ft. (twist/m) |
|-----------------|----------------------|
| 38.09985 | 26.248 |

Mechanical Characteristics (Overall)

UL Temperature Rating: 60°C

8723 Multi-Conductor - Shielded Twisted Pair Cable

| | |
|--|--------------|
| Non-UL Temperature Rating: | 80°C |
| Bulk Cable Weight: | 27.234 Kg/Km |
| Max. Recommended Pulling Tension: | 186.824 N |
| Min. Bend Radius (Install)/Minor Axis: | 40.640 mm |

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

| | |
|---------------------------------------|------------|
| NEC/(UL) Specification: | CM |
| CEC/C(UL) Specification: | CM |
| EU CE Mark: | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 01/01/2004 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |

Flame Test

| | |
|----------------|-------------------|
| UL Flame Test: | UL1685 UL Loading |
|----------------|-------------------|

Plenum/Non-Plenum

| | |
|----------------|---------------------|
| Plenum (Y/N): | No |
| Plenum Number: | 82723, 87723, 88723 |

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

52.000

Nom. Inductance:

Inductance (µH/m)

0.55777

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

108.273

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)

203.422

Nominal Velocity of Propagation:

VP (%)

66

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

48.2307

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 49.215 Ohm/km

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

8723 Multi-Conductor - Shielded Twisted Pair Cable

Current

2.3 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|---------------|----------|-------------|--------|-------|--------------------|
| 8723 060U1000 | 305 MT | 8.618 KG | CHROME | | 2 SH PR #22 PP PVC |
| 8723 060U2000 | 610 MT | 16.329 KG | CHROME | | 2 SH PR #22 PP PVC |
| 8723 060U500 | 152 MT | 4.536 KG | CHROME | | 2 SH PR #22 PP PVC |
| 8723 060100 | 30 MT | 1.452 KG | CHROME | | 2 SH PR #22 PP PVC |
| 8723 0601000 | 305 MT | 8.618 KG | CHROME | C | 2 SH PR #22 PP PVC |
| 8723 06010000 | 3,048 MT | 86.183 KG | CHROME | C Y | 2 SH PR #22 PP PVC |
| 8723 0601640 | 500 MT | 14.878 KG | CHROME | | 2 SH PR #22 PP PVC |
| 8723 0602000 | 610 MT | 18.144 KG | CHROME | C | 2 SH PR #22 PP PVC |
| 8723 0603280 | 1,000 MT | 28.268 KG | CHROME | C | 2 SH PR #22 PP PVC |
| 8723 060500 | 152 MT | 4.309 KG | CHROME | | 2 SH PR #22 PP PVC |
| 8723 0605000 | 1,524 MT | 40.824 KG | CHROME | C | 2 SH PR #22 PP PVC |
| 8723 0609999 | 3,048 MT | 86.183 KG | CHROME | C Y | 2 SH PR #22 PP PVC |

Notes:

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN.MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Revision Number: 2 Revision Date: 07-15-2010

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.