

For more Information  
please call

1-800-Belden1



## Description:

Tinned copper, PVC insulation, medium wall. The extruded PVC insulation is flame and ozone resistant. Inert to most chemicals, oils, and solvents. Covers single cond., PVC insulated hook-up wire for internal wiring of electrical and electronic equipment.

## Physical Characteristics (Overall)

### Conductor

#### AWG:

# Conductors	AWG	Stranding	Conductor Material
1	20	Solid	TC - Tinned Copper

### Insulation

#### Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.4318

### Overall Insulation

#### Overall Cabling

Overall Nominal Diameter: 1.676 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Military Specification:	MIL-W-76C
MIL Spec Rating:	1000 V, 80°C

### Plenum/Non-Plenum

Plenum (Y/N): No

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8529 0021000	305 MT	2.722 KG	RED	P	20 SOL PVC RED
8529 0041000	305 MT	2.722 KG	YELLOW	P	20 SOL PVC YEL
8529 0051000	305 MT	2.722 KG	GREEN, DARK	P	20 SOL PVC GRN
8529 009100	30 MT	0.272 KG	WHITE		20 SOL PVC WHT

## METRIC MEASUREMENT VERSION

### 8529 Hook-up/Lead - (Type MW) MIL-W-76C-PVC

8529 0091000	305 MT	2.722 KG	WHITE	P	20 SOL PVC WHT
8529 010100	30 MT	0.272 KG	BLACK		20 SOL PVC BLK
8529 0101000	305 MT	2.722 KG	BLACK	P	20 SOL PVC BLK
8529 0131000	305 MT	2.722 KG	BLUE, DARK	P	20 SOL PVC DBLU

**Notes:**

P = STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M' FOR 1 OR 2 STRIPES. 10000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL

Revision Number: 1    Revision Date: 05-14-2007

© 2011 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.