

## 8458 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information  
please call

1-800-Belden1



### Description:

22 AWG stranded (7x30) tinned copper conductors, conductors cabled, PVC insulation, PVC Jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Conductors	AWG	Stranding	Conductor Material
15	22	7x30	TC - Tinned Copper

#### Insulation

##### Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.254

#### Outer Shield

##### Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.016

#### Overall Cabling

##### Overall Cabling Lay Length & Direction:

Length (mm)
87.629655

##### Overall Cabling Color Code Chart:

Color
Black
White
Red
Green
Orange
Blue
White/Black
Red/Black
Green/Black
Orange/Black
Blue/Black
Black/White
Red/White
Green/White
Blue/White

Overall Nominal Diameter:

8.001 mm

### Mechanical Characteristics (Overall)

Operating Temperature Range:

-20°C To +80°C

## 8458 Multi-Conductor - Audio, Control and Instrumentation Cable

UL Temperature Rating:	80°C (UL AWM Style 2576)
Bulk Cable Weight:	96.287 Kg/Km
Max. Recommended Pulling Tension:	600.507 N
Min. Bend Radius (Install)/Minor Axis:	83.820 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2576 (150 V 80°C)
CSA Specification:	FT4
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

### Electrical Characteristics (Overall)

#### Nom. Inductance:

Inductance (µH/m)
0.55777

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
111.554

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
51.1836

#### Max. Operating Voltage - UL:

Voltage
300 V RMS (CMG)
150 V RMS (UL AWM Style 2576)

#### Max. Recommended Current:

Current
2.1 Amps per conductor @ 25°C

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8458 060100	30 MT	3.311 KG	CHROME		15 #22 PVC PVC
8458 0601000	305 MT	32.659 KG	CHROME	C	15 #22 PVC PVC
8458 060500	152 MT	16.103 KG	CHROME	C	15 #22 PVC PVC

#### Notes:

C = CRATE REEL PUT-UP.

## 8458 Multi-Conductor - Audio, Control and Instrumentation Cable

Revision Number: 1    Revision Date: 09-18-2008

© 2011 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.