

5500UG Multi-Conductor - Residential, Light Commercial and Institutional Applications

For more Information
please call

1-800-Belden1



Description:

22 AWG stranded (7x30) bare copper conductors, polypropylene insulation, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
2	22	7x30	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PP - Polypropylene	0.1524

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.381

Overall Cabling

Overall Cabling Color Code Chart:

Color
Black
Red

Overall Nominal Diameter: 2.896 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +75°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	10.864 Kg/Km
Max. Recommended Pulling Tension:	80.957 N
Min. Bend Radius (Install)/Minor Axis:	30.480 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
NEC Articles:	800
CEC/C(UL) Specification:	CM
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes

METRIC MEASUREMENT VERSION

5500UG Multi-Conductor - Residential, Light Commercial and Institutional Applications

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT1

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.508555

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
65.62

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
52.8241

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
2.8 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5500UG U4FC1000	152 MT	1.588 KG	BEIGE U4F		2 #22 PP FRPVC
5500UG U4FU500	152 MT	2.041 KG	BEIGE U4F		2 #22 PP FRPVC
5500UG 001C1000	305 MT	3.175 KG	BROWN		2 #22 PP FRPVC
5500UG 001C500	152 MT	1.588 KG	BROWN		2 #22 PP FRPVC
5500UG 001U500	152 MT	2.041 KG	BROWN		2 #22 PP FRPVC
5500UG 003C500	152 MT	1.588 KG	ORANGE		2 #22 PP FRPVC
5500UG 003U500	152 MT	2.041 KG	ORANGE		2 #22 PP FRPVC
5500UG 004C1000	305 MT	3.175 KG	YELLOW		2 #22 PP FRPVC
5500UG 004C500	152 MT	1.588 KG	YELLOW		2 #22 PP FRPVC
5500UG 004U500	152 MT	2.041 KG	YELLOW		2 #22 PP FRPVC
5500UG 005C1000	305 MT	3.175 KG	GREEN, DARK		2 #22 PP FRPVC
5500UG 005C500	152 MT	1.588 KG	GREEN, DARK		2 #22 PP FRPVC
5500UG 005U500	152 MT	2.041 KG	GREEN, DARK		2 #22 PP FRPVC
5500UG 006C500	152 MT	1.588 KG	BLUE, LIGHT		2 #22 PP FRPVC
5500UG 006U500	152 MT	2.041 KG	BLUE, LIGHT		2 #22 PP FRPVC
5500UG 007C1000	305 MT	3.175 KG	VIOLET		2 #22 PP FRPVC
5500UG 007C500	152 MT	1.588 KG	VIOLET		2 #22 PP FRPVC
5500UG 007U500	152 MT	2.041 KG	VIOLET		2 #22 PP FRPVC
5500UG 008C1000	305 MT	3.175 KG	GRAY		2 #22 PP FRPVC

METRIC MEASUREMENT VERSION

5500UG Multi-Conductor - Residential, Light Commercial and Institutional Applications

5500UG 008C500	152 MT	1.588 KG	GRAY		2 #22 PP FRPVC
5500UG 008U1000	305 MT	4.082 KG	GRAY		2 #22 PP FRPVC
5500UG 009C1000	305 MT	3.175 KG	WHITE		2 #22 PP FRPVC
5500UG 009C500	152 MT	1.588 KG	WHITE		2 #22 PP FRPVC
5500UG 009U1000	305 MT	4.082 KG	WHITE		2 #22 PP FRPVC

Revision Number: 1 Revision Date: 05-14-2007

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.