

7923A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable



For more Information
please call

1-800-Belden1

**Description:**

24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, industrial grade sunlight- and oil-resistant PVC jacket, rip cord. Sequential marking at two foot intervals.

Usage (Overall)**Suitable Applications:**

Industrial Ethernet Cable, Harsh Environments, EtherNet/IP™, 350MHz Enhanced Category 5e, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, CMX - Outdoor, RJ-45 Compatible

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
4	24	Solid	BC - Bare Copper	0.508

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PO - Polyolefin	0.2286	0.889

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material
Industrial Grade PVC - Polyvinyl Chloride

Outer Jacket Ripcord:

Yes

Overall Cabling**Overall Nominal Diameter:**

5.842 mm

Pair**Pair Color Code Chart:**

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Storage Temperature Range: -40°C To +85°C

Installation Temperature Range: -25°C To +75°C

Operating Temperature Range: -40°C To +75°C

Bulk Cable Weight: 37.205 Kg/Km

Max. Recommended Pulling Tension: 177.928 N

7923A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

Min. Bend Radius (Install)/Minor Axis:	6.350 mm
--	----------

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR, CMX-Outdoor, UL444
CEC/C(UL) Specification:	CMR
Other Standards:	11801 Category 5
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
PMSHA Specification:	P-07-KA060003
Telecommunications Standards:	568-B.2 Category 5e
Other Specification:	NEMA WC-63.1 Category 5e, UL verified to Category 5e, Ethernet/IP™ Compliant

Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4

Suitability

Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)
49.215

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)
70

Maximum Delay:

Delay (ns/100 m)
510

Max. Delay Skew:

Delay Skew (ns/100 m)
25

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9

Max. Operating Voltage - UL:

Voltage
300 V RMS

7923A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.0	65.3	65.3	63.3	63.3	20.0
4	4.0	56.3	56.3	52.3	52.3	23.6
8	5.7	51.8	51.8	46.1	46.1	25.4
10	6.4	50.3	50.3	43.9	43.9	26.0
16	8.1	47.3	47.3	39.1	39.1	26.0
20	9.2	45.8	45.8	35.2	35.2	26.0
25	10.3	44.3	44.3	34.1	34.1	25.5
31.25	11.6	42.9	42.9	31.3	31.3	25.0
62.5	16.8	38.4	38.4	21.6	21.6	23.5
100	21.7	35.3	35.3	17.1	17.1	22.5
155	27.7	32.5	32.5	4.7	4.7	19.0
200	32.0	30.8	30.8	3.0	3.0	19.0
250	36.4	29.3	29.3	>0	>0	18.0
300	40.5	28.2	28.2	>0	>0	18.0
310	41.3	27.9	27.9			18.0
350	44.3	27.2	27.2			17.0

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	95-110	63.8	60.8
4	100 ± 12	95-110	51.7	48.7
8	100 ± 12	95-107	45.7	42.7
10	100 ± 12	95-107	43.8	40.8
16	100 ± 12	95-107	39.7	36.7
20	100 ± 12	95-107	37.7	34.7
25	100 ± 15	95-107	35.8	32.8
31.25	100 ± 15	95-107	33.9	30.9
62.5	100 ± 15	95-107	27.8	24.8
100	100 ± 15	95-107	23.8	20.8
155	100 ± 18	100 ± 10	19.9	16.9
200	100 ± 20	100 ± 10	17.7	14.7
250	100 ± 20	100 ± 10	15.8	12.8
300	100 ± 20	100 ± 10	14.2	11.2
310	100 ± 20	100 ± 10	13.9	10.9
350	100 ± 22	100 ± 10	12.9	9.9

Notes (Overall)

Notes: US Patent #'s 5, 606, 151; 5, 734, 126. EtherNet IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vendor Association, Inc. Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7923A 0021000	305 MT	12.701 KG	RED	C	4 PR #24 PP PVC
7923A 0101000	305 MT	12.701 KG	BLACK	C	4 PR #24 PP PVC
7923A 0102000	610 MT	24.494 KG	BLACK	C	4 PR #24 PP PVC
7923A 1NH1000	305 MT	12.701 KG	TEAL 1NH	C	4 PR #24 PP PVC

Notes:

C = CRATE REEL PUT-UP.

7923A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

Revision Number: 4 Revision Date: 12-21-2009

© 2011 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.