


9365 Triad - 300V Power-Limited Tray Cable

For more Information
please call

1-800-Belden1

**Description:**

18 AWG triads stranded (19x30) tinned copper conductors, twisted triads, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

| # Triads | AWG | Stranding | Conductor Material |
|----------|-----|-----------|--------------------|
| 1 | 18 | 19x30 | TC - Tinned Copper |

Insulation**Insulation Material:**

| Insulation Material |
|--------------------------|
| PVC - Polyvinyl Chloride |

Insulation Color Code Chart:

| Number | Color |
|--------|-------|
| 1 | Black |
| 2 | White |
| 3 | Red |

Outer Shield**Outer Shield Material:**

| Outer Shield Trade Name | Type | Outer Shield Material | Coverage (%) |
|-------------------------|------|------------------------------|--------------|
| Beldfoil® | Tape | Aluminum Foil-Polyester Tape | 100 |

Outer Shield Drain Wire AWG:

| AWG | Stranding | Drain Wire Conductor Material |
|-----|-----------|-------------------------------|
| 20 | 19x32 | TC - Tinned Copper |

Outer Jacket**Outer Jacket Material:**

| Outer Jacket Material | Nom. Wall Thickness (mm) |
|--------------------------|--------------------------|
| PVC - Polyvinyl Chloride | 0.9398 |

Outer Jacket Ripcord: Yes

Overall Cabling

Overall Nominal Diameter: 6.223 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

Bulk Cable Weight: 58.040 Kg/Km

Max. Recommended Pulling Tension: 329.167 N

Min. Bend Radius (Install)/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

CEC/C(UL) Specification: CMG

AWM Specification: UL Style 2464 (300 V 80°C)

9365 Triad - 300V Power-Limited Tray Cable

| | |
|---------------------------------------|------------|
| EU CE Mark: | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 04/01/2005 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |

Flame Test

| | |
|------------------|------|
| CSA Flame Test: | FT4 |
| IEEE Flame Test: | 1202 |

Suitability

| | |
|-----------------------|-----|
| Suitability - Burial: | Yes |
| Sunlight Resistance: | Yes |

Plenum/Non-Plenum

| | |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

Surface Printing (Overall)**Electrical Characteristics (Overall)****Nom. Characteristic Impedance:**

| |
|-----------------|
| Impedance (Ohm) |
| 45 |

Nom. Inductance:

| |
|-------------------|
| Inductance (μH/m) |
| 0.55777 |

Nom. Capacitance Conductor to Conductor:

| |
|--------------------|
| Capacitance (pF/m) |
| 177.174 |

Nom. Capacitance Cond. to Other Conductor & Shield:

| |
|--------------------|
| Capacitance (pF/m) |
| 331.381 |

Nom. Conductor DC Resistance:

| |
|---------------------|
| DCR @ 20°C (Ohm/km) |
| 19.5548 |

Nominal Outer Shield DC Resistance:

| |
|---------------------|
| DCR @ 20°C (Ohm/km) |
| 26.248 |

Max. Operating Voltage - UL:

| |
|-----------|
| Voltage |
| 300 V RMS |

Max. Recommended Current:

| |
|-------------------------------|
| Current |
| 5.5 Amps per conductor @ 25°C |

Related Documents:

No related documents are available for this product

Put Ups and Colors:

METRIC MEASUREMENT VERSION

9365 Triad - 300V Power-Limited Tray Cable

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|---------------|--------|-------------|--------|-------|------------------|
| 9365 060U1000 | 305 MT | 18.144 KG | CHROME | | 3 #18 PVC FS PVC |
| 9365 060U500 | 152 MT | 9.299 KG | CHROME | | 3 #18 PVC FS PVC |
| 9365 0602500 | 762 MT | 45.359 KG | CHROME | | 3 #18 PVC FS PVC |

Revision Number: 2 Revision Date: 04-07-2009

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.