



For more Information
please call

1-800-Belden1



Description:

20 AWG pairs stranded (19x32) tinned copper conductors, twisted pairs, PVC insulation, unshielded, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	20	19x32	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PVC - Polyvinyl Chloride	1.7272

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.9398

Outer Jacket Ripcord: Yes

Overall Cabling

Overall Cabling Lay Length & Direction:

Direction
Left-hand Lay

Overall Nominal Diameter: 5.436 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

Bulk Cable Weight: 34.229 Kg/Km

Max. Recommended Pulling Tension: 137.894 N

Min. Bend Radius (Install)/Minor Axis: 50.800 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: PLTC, ITC, CMG

CEC/C(UL) Specification: CMG

9408 Multi-Conductor - 300V Power-Limited Tray Cable

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 FT4 Loading

C(UL) Flame Test: FT4

IEEE Flame Test: 1202

ICEA Flame Test: T-29-520

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Burial: Yes

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance ($\mu\text{H/m}$)

0.62339

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

180.455

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

98.43

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

31.1695

Max. Operating Voltage - UL:

Voltage

300 V RMS (PLTC)

CMG)

150 V RMS (ITC)

Max. Recommended Current:

Current

7.6 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

METRIC MEASUREMENT VERSION

9408 Multi-Conductor - 300V Power-Limited Tray Cable

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9408 060U1000	305 MT	10.433 KG	CHROME		2 #20 PVC PVC
9408 060U500	152 MT	5.443 KG	CHROME		2 #20 PVC PVC
9408 0602500	762 MT	26.082 KG	CHROME		2 #20 PVC PVC

Revision Number: 1 Revision Date: 05-14-2007

© 2011 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.