

For more Information  
please call

1-800-Belden1



## Description:

23 AWG Solid .023" bare copper-covered steel conductor, plenum, FEP insulation, bare copper braid shield (97% coverage), FEP jacket.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	23	Solid	BCCS - Bare Copper Covered Steel	0.5842

### Insulation

Insulation Material:

Insulation Material	Dia. (mm)
FEP - Fluorinated Ethylene Propylene	3.3528

### Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	97

### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

### Overall Cabling

Overall Nominal Diameter: 4.826 mm

## Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Non-UL Temperature Rating: 200°C

Bulk Cable Weight: 53.575 Kg/Km

Max. Recommended Pulling Tension: 275.788 N

Min. Bend Radius (Install)/Minor Axis: 63.500 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	59/U

### Flame Test

UL Flame Test:	NFPA 262
C(UL) Flame Test:	FT6

### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes

### Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	8241

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

Impedance (Ohm)
75

### Nom. Inductance:

Inductance (µH/m)
0.413406

### Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
63.9795

### Nominal Velocity of Propagation:

VP (%)
69.5

### Nominal Delay:

Delay (ns/m)
4.75745

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
160.769

### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
8.5306

### Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	1.6405
10	3.281
50	7.5463
100	10.8273
200	17.0612
400	27.5604
700	38.0596
900	45.2778
1000	48.5588

### Max. Operating Voltage - UL:

Voltage
300 V RMS

**Max. Operating Voltage - Non-UL:**

<b>Voltage</b>
1700 V RMS

**Related Documents:**

No related documents are available for this product

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
88241 0101000	305 MT	16.329 KG	BLACK	C	23 SH FEP RG-59/U COAX
88241 010500	152 MT	8.165 KG	BLACK	C	23 SH FEP RG-59/U COAX

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 1    Revision Date: 05-14-2007

© 2011 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.