



For more Information  
please call

1-800-Belden1



### Description:

22 AWG solid tinned copper conductors, polypropylene insulation, twisted pair, overall Beldfoil shield (100% coverage), 22 AWG solid TC drain wire, PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
1	22	Solid	TC - Tinned Copper

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PP - Polypropylene	0.1778

#### Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
22	Solid		TC - Tinned Copper

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.4572

#### Overall Cabling

Overall Nominal Diameter: 2.997 mm

#### Pair

Pair Color Code Chart:

Number	Color
1	Black & Red

### Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +105°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 17.858 Kg/Km

Max. Recommended Pulling Tension: 164.583 N

Min. Bend Radius (Install)/Minor Axis: 30.480 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification: CM

CEC/C(UL) Specification: CM

EU CE Mark:	Yes
-------------	-----

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
---------------------------------	-----

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
---------------------------------------	------------

EU Directive 2002/96/EC (WEEE):	Yes
---------------------------------	-----

EU Directive 2003/11/EC (BFR):	Yes
--------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
-----------------------------------	-----

MII Order #39 (China RoHS):	Yes
-----------------------------	-----

**Flame Test**

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

**Plenum/Non-Plenum**

Plenum (Y/N):	No
---------------	----

**Electrical Characteristics (Overall)****Nom. Characteristic Impedance:**

Impedance (Ohm)

40

**Nom. Inductance:**Inductance ( $\mu\text{H/m}$ )

0.26248

**Nom. Capacitance Conductor to Conductor:**

Capacitance (pF/m)

131.24

**Nom. Capacitance Cond. to Other Conductor & Shield:**

Capacitance (pF/m)

249.356

**Nominal Velocity of Propagation:**

VP (%)

66

**Nominal Delay:**

Delay (ns/m)

4.9215

**Nom. Conductor DC Resistance:**

DCR @ 20°C (Ohm/km)

52.8241

**Nominal Outer Shield DC Resistance:**

DCR @ 20°C (Ohm/km)

41.5047

**Max. Operating Voltage - UL:**

Voltage

300 V RMS

**Max. Recommended Current:**

Current

2.9 Amps per conductor @ 25°C

**Notes (Overall)**

**Notes:** Belden's® Miniature Type Broadcast Audio and Instrumentation Cables occupy 1/2 to 2/3 less space than standard cables.

**Related Documents:**

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8450 0081000	305 MT	5.897 KG	GRAY		2 #22 PP SHLD PVC FR
8450 010U1000	305 MT	6.350 KG	BLACK		2 #22 PP SHLD PVC FR
8450 010U500	152 MT	3.402 KG	BLACK		2 #22 PP SHLD PVC FR
8450 0101000	305 MT	5.897 KG	BLACK		2 #22 PP SHLD PVC FR

Revision Number: 1    Revision Date: 05-14-2007

© 2011 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.