

# Cobarib



- Manufactured from hard-wearing natural rubber
- Slip-resistant 'fluted' surface
- Provides insulation from cold concrete floors
- Can also be used on workbenches to prevent fragile parts from damage

#### Technical Specifications:

- Product height: 3mm & 6mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.9 x 10 (3mm)	30	20 x 20 x 90	Roll	1	20	Black	RR010010
0.9 x per linear metre (3mm)	3	2 x 2 x 90	Roll	1	N/A	Black	RR010010C
1.2 x 10 (3mm)	40	20 x 20 x 120	Roll	1	20	Black	RR010020
1.2 x per linear metre (3mm)	4	2 x 2 x 120	Roll	1	N/A	Black	RR010020C
0.9 x 10 (6mm)	73	28 x 28 x 90	Roll	1	9	Black	RR010030
0.9 x per linear metre (6mm)	6	28 x 28 x 90	Roll	1	N/A	Black	RR010030C
1.2 x 10 (6mm)	8	28 x 28 x 120	Roll	1	9	Black	RR010040
1.2 x per linear metre (6mm)	8	28 x 28 x 120	Roll	1	N/A	Black	RR010040C

Material: Natural rubber  
 Surface Finish: Fine fluted ribbed surface  
 Product Height: 3 mm and 6 mm nominal

Operating Temperature: -20° to 160° C

Resistance to Chemicals: Resistant to water and most mild acids  
 Environmental Resistance: Use in wet or dry areas.  
 UV Resistance: Yes

Typical Applications: Industrial uses around benches, workstations and walkways. Also suitable for use as a covering for bench work surfaces.

Installation Method: Loose lay  
 Cleaning method: Hose down or pressure wash using a mild detergent.

Continued on next page

Product Performance:	Fatigue: Slip Resistance: Wear: Low ‡ High	
Flame Retardancy:	N/A	
Country of Origin:	China	

End of document