

1250 Rocker Switches 10A 250Vac



10(6)A 250Vac T100
6A 400Vac T100
1A 30Vdc



UL CSA 10A 250Vac
UL CSA 16A 250Vac Resistive
UL CSA 125Vac 1/2hp
UL CSA 1A 30Vdc
UL 100°C, file E45221, CSA file LR10990

In house test

Inrush 75A to EN61058-1 & 10A 28Vdc



RoHS compliant

3mm contact gap
Technical data on pages 4 & 5

- Standard rocker switch
- Double pole in single pole body
- Snap in or sub panel mount
- Integral terminal barrier
- Push on or PCB terminals
- High inrush tolerance
- Bezel size:
29.5 x 15mm (snap in)
23.5 x 13mm (sub panel mount)



C1250AP



C1250AN

C 1250 A P B B 085W

B BLACK
W WHITE

B BLACK
W WHITE
G GREY


TERMINAL CODE FUNCTION CODE ROCKER CODE BODY CODE BODY COLOR ROCKER COLOR LEGEND & OPTIONS

ORDER FORMAT


TERMINAL	FUNCTION	ROCKER	BODY	OPTIONS
<p>C</p> <p>6.3 x 0.8</p>	<p>On when pressed over terminal 1</p> <p>1250</p> <p>ON - OFF Double pole</p> <p>Poles are 9.0mm between centres.</p>	<p>A Curved</p> <p>Shown in N body</p>	<p>N</p> <p>Panel cut-out Bezel</p> <p>Sub-panel Facia</p> <p>Panel thickness Dim X</p> <p>0.75-1.24 26.1/26.2 1.25-1.99 26.3/26.4 2.00-3.00 26.7/26.8</p>	<p>Finish Matt finish only</p> <p>Color Call factory for custom colors. A full range is available for large orders</p> <p>Legend printing Select from the examples or call factory for custom legends</p>
<p>X</p> <p>PCB 0.8sq (N body only)</p>	<p>On when pressed over terminal 1</p> <p>1250SP</p> <p>ON - OFF Single pole</p>	<p>P</p> <p>Panel cut-out Bezel</p> <p>Panel thickness</p> <p>0.75-3.00</p>	<p>Cut-outs must be punched in the direction of insertion</p>	

Dimensions (mm)


1250AN (C terminals shown)



1250AN (X terminals shown)



1250AP (C terminals shown)



Examples of our range of legend printing

() is legend color B-Black, W-White, R-Red



085(B)



086(B)