

[PRODUCT OVERVIEW](#) [ELECTRONIC TOOLS](#) [OSCILLOSCOPE PROBE SETS](#)

## OSCILLOSCOPE PROBE 250MHz

**PROBE250**



### Features

- complete probe set, for measurements up to 250MHz
- attenuation: 1:1 or 1:10
- safety: conform to IEC-1010 cat II

### Specifications

- position x1:
  - attenuation: 1:1
  - bandwidth: DC to 10MHz
  - rise time: 35ns
  - input resistance: 1Mohm (input resistance scope)
  - input capacitance: cap. scope 46pF
  - working voltage: 600Vdc incl. peak AC derating with frequency
  - position REF: tip disconnected, scope input at ground
- position x10:
  - attenuation: 1:10
  - bandwidth: DC to 250MHz
  - rise time: 1.4ns
  - input resistance: 10Mohm (if scope input = 1Mohm)
  - input capacitance:  $\pm 11$ pF
  - working voltage: 600Vdc incl. peak AC derating with frequency
  - compensation range: 10 to 35pF
- cable length: 1.2m

### Packaging information



**Type of packaging:**

Plastic Bag



**Bar code (EAN-13):**

5410329222062

*All registered trademarks and trade names are properties of their respective owners and are used only for the clarification of the compatibility of our products with the products of the different manufacturers. Due to constant product improvements the actual product appearance might differ from the shown images. Product images are for illustrative purposes only.*