## **ALPHA WIRE CUSTOMER PRODUCT SPECIFICATION**

Part Number: B954024 Page 1 of 2 Pages				Issue: 1 Issue Date: 8/23/2010 Effective Date: 10/18/2010						
Α.			uction					Diameters (mm)		
	1)	a) b)	nponent 1 Conductor Insulation (1) Color Code	2 X 1 COND 22 (7/30) AWG TC 0.25 Wall, Nom. PVC, Semi I Alpha Wire Color Code E	Rigid			0.76 1.27		
			Cond Color	Cond Color		Cond	Color			
			1 BLACK	2 BROWN						
	2)	a)	ble Assembly Twists:	2 Components Cabled 39.4 Twists/meter (min)	A Min					
	3)	b) Shi a)	Core Wrap eld: Drain Wire	Clear Mylar Tape, 25% Over A/P/A Tape, 25% Overlap, N 22 (7/30) AWG TC						
	4)	b) Jac a) b)	Color(s) Ripcord	TC,70% Coverage, Min. 0.81 Wall, Nom.,PVC GREY 1 End 810 Denier Nylon				4.95 (5.21 Max.)		
		c)	Print			105C O (SEQ N				
В.	Ap	olica	ble Specifications	* = Factory Code						
	1)	UL								
		a) b)	Component 1 Overall	AWM/STYLE 10002 AWM/STYLE 2464 CM VW-1		°C / 300 C / 300 \ °C				
	2)	IEC	;	EN 60332-1 Flame Behavior EN 60332-2 Flame Behavior						
	3)	CE		LVD 73/23/EEC Amendment	93/68/EE	3/68/EEC				
	<ul> <li>Environmental Compliance</li> <li>EU Directive 2002/95/EC(RoHS):</li> </ul>									
	.,	All materials used in the manufacture of this part are in compliance with EL Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's w for compliance Date of Manufacture.							b site	
	2)	RE	ACH Regulation (EC 1	007/2006): This product does not contain REACH Substance of Very H 2010, in excess of a concent	ligh Conce	ern (SVI	HC) ca	andidate list, dated 30 Ma		
D.	Phy	ysica	al & Mechanical Prope				.g			
	1)		nperature Range	-30 to 105°C						
	2) 3)		nd Radius I Tension	10X Cable Diameter 19.1 Lbs, Maximum						
	3) 4)		nlight Resistance	Yes						
			al Properties	(For Engineering purposes of	only)	()				
	1)	Vol	tage Rating	300 V <sub>RMS</sub>						
	2)		pacitance	127.92 pf/m @1 kHz, Nomin		ctor to C	conduc	ctor		
	3) 4)		ound Capacitance	229.6 pf/m @1 kHz, Nomina	ll					
	4) 5)									
	6)	Cor	nductor DCR	53.792 Ω/Km @20°C, Nomi						
	7)	OA	Shield DCR	15.088 Ω/Km @20°C, Nomi	nal					
Althou	4) 5) 6) 7)	Cha Ind Cor OA	aracteristic Impedance uctance nductor DCR Shield DCR Wire Company ("Alpha") mak	48 Ω 0.5904 μH/m, Nominal	nal nal					

described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

## **ALPHA WIRE** CUSTOMER PRODUCT SPECIFICATION

Part Number: B954024	Issue:	1
Page 2 of 2 Pages	Issue Date:	8/23/2010
	Effective Date:	10/18/2010

## F. Other

b)

C)

d)

1) Packaging Flange x Traverse x Barrel (inches) 18 x 12 x 8 Continuous length a) 3280 FT 12 x 12 x 3.5 Continuous length 1640 FT 10 x 4 x 3.5 Continuous length 6.5 x 4 x 2.5 Continuous length 328 FT 164 FT [Spool dimensions may vary slightly]

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.