ALPHA WIRE CUSTOMER PRODUCT SPECIFICATION

		umber: B96 of 2 Pages				ue: ue Date ective [1 9/10/2010 11/5/2010	
A.	Со	nstruction						Diameters (mm)	
	1)	Component a) Condu b) Insulati (1) Co	ctor	4 X 1 PAIR 22 (7/30) AWG TC 0.25 Wall, Nom. PVC, Se Alpha Wire Color Code B				0.76 1.27	
		Pair 1	Color WHITE-BLACK	Pair Color 3 WHITE-RED		Pair	Color		
		2	WHITE-BROWN	4 WHITE-ORANGE					
	2) 3)	c) Pair (1) Tv Cable Asse a) Twists: b) Core W Shield:	mbly	2/Cond Cabled Together 26.2 Twists/meter (min) 4 Components Cabled 17.5 Twists/meter (min) Clear Mylar Tape, 25% O Alum/Mylar Tape, 25% O					
		a) Foil Dir		Foil Facing In					
	4)	 b) Drain V Jacket a) Color(s b) Ripcord c) Print 	3)	22 (7/30) AWG TC 0.81 Wall, Nom.,PVC GREY 1 End 810 Denier Nylon ALPHA WIRE-* P/N B964 0.35MM2 (22AWG) (U VW-1 CE * = Factory Code		105C O (SEQ I			
в.	Ap	plicable Spe	cifications						
	1)	UL							
		a) Compo b) Overall		AWM/STYLE 10002 AWM/STYLE 2464 CM VW-1		°C / 300 C / 300 \ °C			
	2)	IEC		EN 60332-1 Flame Behav EN 60332-2 Flame Behav	vior	-0			
C	3) Env	CE: vironmental	Compliance	LVD 73/23/EEC Amendm	ient 93/68/EE	=C			
0.	. Environmental Compliance 1) EU Directive 2002/95/EC(RoHS):								
				for compliance Date of Ma	arding the re	striction	of use		e
	2)	REACH Re	gulation (EC 19	This product does not cor				listed on the European Unic Indidate list, dated 30 March	
_				2010, in excess of a conc					
D.	Phy 1)	ysical & Meo Temperatur	chanical Prope	-30 to 105°C					
	2)	Bend Radiu		10X Cable Diameter					
	3)	Pull Tensio	n	49 Lbs, Maximum					
-	4)	Sunlight Re		Yes					
Ε.	Ele	ctrical Prop Voltage Rat		(For Engineering purpos 300 V _{RMS}	es only)				
	2)	Mutual Cap		88.56 pf/m @1 kHz, Non	ninal				
	3)	Ground Ca	pacitance	160.72 pf/m @1 kHz, No	ominal				
	4) 5)	Characteris Inductance	tic Impedance	70 Ω 0.5904 μH/m, Nominal					
Althr	,		pany ("Alnha") mak	•	s every reasonable effort to ensure their accuracy at the time of publication, information and specifications				
desc prod Alph	ribed uct av a prov	herein are subje vailability. vides the informa	ect to errors or omis ation and specificati	sions and to changes without notice, ons herein on an "AS IS" basis, with	and the listing on representation	of such info	rmation anties, w	and specifications does not ensure /hether express, statutory or implied	I. Ir
beer	advis	sed of the possib	pility of such damag	(including consequential, indirect, in es, whether in an action under contra cifications described herein.					

ALPHA WIRE CUSTOMER PRODUCT SPECIFICATION

	rt Number: B964042 Ige 2 of 2 Pages	Issue: 1 Issue Date: 9/10/2010 Effective Date: 11/5/2010
F.	 Conductor DCR OA Shield DCR Other 	54.776 Ω/Km @20°C, Nominal 38.704 Ω/Km @20°C, Nominal
 Packaging 3280 FT 1640 FT 328 FT 164 FT 		Flange x Traverse x Barrel (inches) 24 x 14 x 12 Continuous length 18 x 12 x 8 Continuous length 12 x 4.5 x 3.5 Continuous length 10 x 4 x 3.5 Continuous length [Spool dimensions may vary slightly]

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.