

**Farnell Order Code: 1538942**  
**FOX MODEL: FXO-HC735R-200**  
**FOX Part Number: 768-200-35**  
**HCMOS, CERAMIC, SMD, OSCILLATOR**

**A. Specifications**

Parameters	
Frequency	200 MHz
Frequency Stability <sup>1</sup>	±50 PPM
Temperature Range	
Operating (T <sub>OPR</sub> )	-40°C ~ +85°C
Storage (T <sub>STG</sub> )	-55°C ~ +125°C
Supply Voltage (V <sub>DD</sub> )	3.3V ± 5%
Input Current (I <sub>DD</sub> )	55 mA Max
Output Voltage (V <sub>OL</sub> ) (V <sub>OH</sub> )	20% V <sub>DD</sub> Max 80% V <sub>DD</sub> Min
Output Symmetry (50% V <sub>p-p</sub> Level)	45% ~ 55%
Rise Time (20% ~ 80% V <sub>p-p</sub> ) (TR)	2 nS Max
Fall Time (80% ~ 20% V <sub>p-p</sub> ) (TF)	2 nS Max
Output Load (HCMOS)	15 pF Max
Startup Time (T <sub>S</sub> )	10 ms Max
Output Enable / Disable Time <sup>2</sup>	100 nS Max
Phase Jitter (12kHz ~ 20MHz)	0.67 pS Typ.
Maximum Soldering Temp / Time	260°C / 10 Seconds
Moisture Sensitivity Level (MSL)	1
Termination Finish	Au

<sup>1</sup> Inclusive of 25°C tolerance, operating temperature range, input voltage change, load change, aging, shock, and vibration.

<sup>2</sup> An internal pullup resistor from pin 1 to pin 4 allows active output if pin 1 is left open.

ENABLE/DISABLE FUNCTION <sup>2</sup>	
Pin 1	OUTPUT (Pin 3)
OPEN <sup>c</sup>	ACTIVE
'1' Level V <sub>IH</sub> ≥ 70%V <sub>DD</sub>	ACTIVE
'0' Level V <sub>IL</sub> ≤ 30%V <sub>DD</sub>	High Z

**NOTE** A 0.01µF bypass capacitor should be placed between V<sub>DD</sub> (Pin4) and GND (Pin 2) to minimize power supply line noise.


**RoHS Compliance Status: Compliant**



Drawing is for reference to critical specifications defined by size measurements. Certain non-critical visual attributes, such as side castellations, reference pin shape, etc. may vary

**NOTE** The above specifications, having been carefully prepared and checked, is believed to be accurate at the time of publication; however, no responsibility is assumed by Fox Electronics for inaccuracies.


**B. Mechanical / Dimensions (millimeters):**



Note: XRESSO HCMOS XOs are designed to fit on industry standard, 4 pad, layouts.

**Pin Connections**  
 #1) E/D    #3 Output  
 #2) GND    #4 VDD  
 \*TP are test points and are NC

**Recommended Circuit**



Reference / Comments	Title / Description: Product Specifications		
	Drawing Number: DWG-4549-5	Rev: 1	Size: A
	Part Number: 768-200-35		Cage: 61429
	Draftsperson: AR	Approved: BN	Date: 01/15/2008