





1 2 3 4 5



A-A Section



PCB LAYOUT - COMPONENT VIEW

TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: NYLON 9T
 FLAMABILITY RATING: UL94-V0
 COLOR: BEIGE
 CONTACT MATERIAL: COPPER ALLOY
 CONTACT TYPE: STAMPED
 CONTACT PLATING: TIN
 QUALITY CLASS: 25 MATING CYCLES
 PITCH: 2.00MM

ENVIRONMENTAL
 OPERATING TEMPERATURE: -25 UP TO 85°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 2A
 WORKING VOLTAGE: 125V AC
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 800V AC/MN
 CONTACT RESISTANCE: 20 mOHM MAX

STANDARD
 IEC CERTIFIED: E323964 / MODEL NUMBER 6201xx-131822

SOLDERING
 REFLOW PROCESS

PACKAGING
 TAPE AND REEL

DIMENSION
 A = 2.00 x (NB PIN - 1)
 B = 2.00 x (NB PIN-1) + 6

A

B

C

G			
F			
E			
D	19-APR-11	PINS WIDTH	GG
C	17-NOV-09	STANDARD	JP
B	28-JAN-09	B DIMENSION	JP
A	23-JUN-08	PDF	CH
REV	DATE	FILE	BY


PROJECTION:	
APPROVAL: RJ	

GENERAL TOLERANCE
.X = +/- 0.2
.XX = +/- 0.15
UNIT: MM
SCALE:
SHEET: 1/2
DRAW:


DESCRIPTION: 2.00 SMT MALE HORIZONTAL SHROUDED HEADER	
WERI PART NO: 620 1xx 131 822	

SIZE
A4

D



Material: Black Anti-static Polystyrene
 Q,TY: 800 PCS / REEL



Poles	A	B
2	8.40	24.00
3	10.40	
4	12.40	
5	14.40	
6	16.40	32.00
7	18.40	
8	20.40	44.00
9	22.40	
10	24.40	
11	26.40	
12	28.40	
13	30.40	
14	32.40	
15	34.40	
16	36.40	

G			
F			
E			
D			
C			
B			
A	23-JUN-08	PDF	CH
REV	DATE	FILE	BY

PROJECTION:	GENERAL TOLERANCE		DESCRIPTION: 2.00 SMT MALE HORIZONTAL SHROUDED HEADER WERI PART NO: 6201 xx 131822	SIZE A4
	.X = +/- 0.2 .XX = +/- 0.15			