


- Smooth barrel, Ø 6.5 mm
- Stainless steel, 1.4404
- Factor 1 for all metals
- Protection class IP68
- Magnetic field immune
- High switching distance
- High switching frequency
- Recessed mounting possible
- DC 3-wire, 10...30 VDC
- NO contact, PNP output
- Cable connection

**Wiring diagram**



**Functional principle**



Inductive sensors detect metal objects contactless and wear-free. uprox®+ sensors have considerable advantages due to their patented multi-coil system. They excel in highest switching distances, maximum flexibility and operational reliability as well as efficient standardization.

<b>Type</b>	BI2U-EH6,5-AP6X
Ident-No.	4281150
<b>Rated operating distance Sn</b>	2 mm
Mounting condition	flush
Assured sensing range	≤ (0,81 x Sn) mm
Repeatability	≤ 2 %
Temperature drift	≤ ± 10 %
Hysteresis	3...15
Ambient temperature	-30...+85
<b>Operating voltage</b>	10...30
Residual ripple	≤ 10 % U <sub>SS</sub>
DC rated operational current	≤ 150 mA
No-load current I <sub>0</sub>	≤ 15 mA
Residual current	≤ 0.1 mA
Rated insulation voltage	≤ 0.5 kV
Short-circuit protection	yes/ cyclic
Voltage drop at I <sub>e</sub>	≤ 1.8 V
Wire breakage / Reverse polarity protection	yes/ complete
Output function	3-wire, NO contact, PNP
Protection class	☐
Switching frequency	≤ 2 kHz
<b>Design</b>	smooth barrel, 6.5 mm
Dimensions	41.6
Housing material	Metal, V2A (1.4301)
Material active face	Plastic, PP-GF30
End cap	Plastic, PP
Connection	cable
Cable quality	4 mm, LiYY-11Y, PUR, 2m
Cable cross section	3 x 0.25
Vibration resistance	55 Hz (1 mm)
Shock resistance	30 g (11 ms)
Protection class	IP68
<b>Switching state</b>	LED yellow

Mounting instructions	minimum distances
Distance D	13 mm
Distance W	6 mm
Distance T	20 mm
Distance S	10 mm
Distance G	12 mm

---

<b>Diameter of the active area B</b>	Ø 6.5 mm
--------------------------------------	----------



Flush and recessed mounting of all uprox<sup>®</sup>+ threaded barrel sensors. Safe operation is ensured if the sensor is screwed in 0.5 mm.