

# XMLA004A2S11

pressure switch XMLA 4 bar - fixed scale 1  
threshold - 1 C/O



## Main

|   |  |
|---|--|
| Range of product  | OsiSense XM  |
| Product or component type                               | Electromechanical pressure sensor  |
| Pressure sensor type                                    | Electromechanical pressure sensor  |
| Pressure sensor name                                    | XMLA   |
| Cable entry   | 1 entry tapped for Pg 13.5 cable gland, cable outer diameter: 9...13 mm  |
| Contacts type and composition                           | 1 C/O  |
| Electrical circuit type                                 | Control circuit  |
| Controlled fluid  | Air (0...70 °C)<br>Fresh water (0...70 °C)<br>Hydraulic oil (0...70 °C)<br>Sea water (0...70 °C)                     |
| Electrical connection                                   | Screw-clamps terminals 1 x 0.2...2 x 2.5 mm <sup>2</sup>   |
| Fluid connection type                                   | G 1/4 (female) conforming to ISO 228   |
| Pressure sensor size                                    | 4 bar  |
| Scale type  | Fixed differential   |
| Local display   | With   |
| Pressure switch type of operation                       | Detection of 1 single threshold  |
| Product specific application                            | -  |
| Adjustable range of switching point on rising pressure  | 0.4...4 bar  |
| Adjustable range of switching point on falling pressure | 0.05...3.65 bar  |
| Maximum permissible accidental pressure                 | 9 bar  |
| Destruction pressure                                    | 18 bar   |
| Pressure actuator                                       | Diaphragm  |
| Materials in contact with fluid                         | Nitrile<br>Zinc alloy  |
| Enclosure material                                      | Zinc alloy   |
| [In] rated current                                      | B300, AC-15 (U <sub>e</sub> = 120 V)<br>B300, AC-15 (U <sub>e</sub> = 240 V)<br>R300, DC-13 (U <sub>e</sub> = 250 V) |

## Complementary

|  |   |
|--|---|
| Natural differential at low setting      | 0.35 bar (+/- 0.03 bar)   |
| Natural differential at high setting     | 0.35 bar (+/- 0.03 bar)   |
| Maximum permissible pressure - per cycle | 5 bar   |
| Terminal block type                      | 4 terminals   |
| Operating rate                           | <= 120 cyc/mn at > 0 °C   |
| Repeat accuracy                          | < 2 %   |
| [Ui] rated insulation voltage            | 300 V conforming to CSA C22-2 No 14<br>300 V conforming to UL 508<br>500 V conforming to EN/IEC 60947-1 |
| [Uimp] rated impulse withstand voltage   | 6 kV conforming to EN/IEC 60947-1   |
| Auxiliary contacts operation             | Snap action   |
| Contacts material                        | Silver contacts   |

|                               |  |
|-------------------------------|--|
| Resistance across terminals   | < 25 mOhm conforming to IEC 255-7 category 3<br>< 25 mOhm conforming to NF C 93-050 method A |
| Short circuit protection      | 10 A cartridge fuse type gG (gl)   |
| Mechanical durability         | 8000000 cycles   |
| Setting                       | External   |
| Terminals description ISO n°1 | (13-14-11-12)OF  |
| Height                        | 75 mm  |
| Depth                         | 113 mm   |
| Width                         | 35 mm  |
| CAD overall depth             | 75 mm  |
| CAD overall height            | 113 mm   |
| CAD overall width             | 35 mm  |
| Product weight                | 0.685 kg   |

## Environment

|  |   |
|--|---|
| Standards                                  | CE<br>CSA C22-2 No 14<br>EN/IEC 60947-5-1<br>UL 508   |
| Product certifications                     | BV<br>CCC<br>CSA<br>DNV (Det Norske Veritas)<br>GL<br>LROS (Lloyds register of shipping)<br>RINA<br>UL<br>VIT-SEPRO |
| Protective treatment                       | TC  |
| Ambient air temperature for operation      | -25...70 °C   |
| Ambient air temperature for storage        | -40...70 °C   |
| Operating position                         | Any position  |
| Vibration resistance                       | 4 gn (f = 30...500 Hz) conforming to IEC 68-2-6   |
| Shock resistance                           | 50 gn conforming to IEC 68-2-27   |
| Class of protection against electric shock | Class I conforming to IEC 1140<br>Class I conforming to IEC 536<br>Class I conforming to NF C 20-030                |
| IP degree of protection                    | IP66 conforming to EN/IEC 60529   |