

CH20M CH20M22 B BK/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-2083 www.weidmueller.com



Superior efficiency, flexibility and design - the "standard tailor-made fit"

When selecting a housing design, flexibility is a key factor. Other important criteria are: scalability, customized design, innovative functionality and cost efficiency. You need a choice which offers the maximum performance with the minimum overhead.

The CH20M22 modular electronics housing is the standard format from amongst the different housing widths. It has the optimal width for most typical electronics applications.

The entire system is characterized by excellence: outstanding scalability and flexibility, a high security level, innovative application functionality and a variety of practical details.

- Quicker installation with features such as "Wire ready" the universal multi-tool screw head
- User-friendly operations: with clear and permanent labelling and extra marking possibilities, integrated release clip or transparent cover
- Maximum interference immunity with EMC-compliant construction featuring deeply overlapping module joint edges made from high-performance plastic
- High operational reliability with the unique Auto-Set coding system and featuring double-sided touch protection on the pin header and socket blocks

CH20M - a compact name for the most flexible system available on the market. It doesn't just stand for "Component Housing IP20 Modular".

CH20M also stands for efficiency and innovation throughout design, production and use.

Note: technical specifications are preliminary

General ordering data

| Order No. | <u>2418630000</u> |
|-----------|---|
| Туре | CH20M22 B BK/BK |
| Version | Electronics housings, CH20M black, Base element, Width: 22.5 mm |
| EAN | 4032248897742 |
| Qty. | 10 pc(s). |
| | |



CH20M CH20M22 B BK/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-2083 www.weidmueller.com

Technical data

Dimensions

| Length | 107.4 mm | Width | 22.5 mm |
|--------|----------|-------|---------|
| Height | 109.3 mm | | |

System parameters

| Version | Base element | Type of connection | without | |
|-----------------------------|--------------|--------------------------|---------|--|
| Number of PCBs per module | 1 | PCB thickness | 1.6 mm | |
| Tolerance for the PCB shape | ±0.15 mm | Contact to terminal rail | No | |
| Encapsulation option | No | | | |

Material data

| Flammability class UL 94 | V-0 | Insulating material | PA 66 GF 30 | |
|----------------------------------|-------|----------------------------------|-------------|--|
| Colour | black | Continuous operating temp., min. | -20 °C | |
| Continuous operating temp., max. | 85 °C | | | |

Classifications

| eClass 6.0 | 90-27-26-07 | | |
|------------|-------------|--|--|

Approvals

Approvals



CH20M CH20M22 B BK/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-2083 www.weidmueller.com

Drawings

