ALPHA WIRE CUSTOMER PRODUCT SPECIFICATION

Part Number: B956204 Issue:

Page 1 of 2 Pages 9/7/2010 **Issue Date: Effective Date:** 11/2/2010

A. Construction Diameters (mm)

20 X 1 COND 1) Component 1

18 (16/30) AWG TC Conductor 1.19 Insulation 0.41 Wall, Nom. PVC 2.01

(1) Color Code Alpha Wire Color Code D

Cond	Color	Cond	Color	Cond	Color
1	BLACK	8	YELLOW	15	RED/BLACK
2	RED	9	VIOLET	16	WHITE/BLACK
3	WHITE	10	SLATE	17	WHITE/RED
4	GREEN	11	PINK	18	WHITE/GREEN
5	ORANGE	12	TAN	19	WHITE/YELLOW
6	BLUE	13	RED/GREEN	20	WHITE/BLUE
7	BROWN	14	RED/YELLOW		

2) Cable Assembly 20 Components Cabled Twists: 7.9 Twists/meter (min)

Core Wrap Clear Mylar Tape, 25% Overlap, Min. b) Shield: A/P/A Tape, 25% Overlap, Min.

Drain Wire 20 (7/28) AWG TC a) b) Braid TC,70% Coverage, Min.

Jacket 0.81 Wall, Nom., PVC 12.98 (13.48 Max.)

a) Color(s) **GREY**

Ripcord 1 End 810 Denier Nylon b) ALPHA WIRE-* P/N B956204 c) Print

> 0.81MM2 (18AWG) (UL) TYPE CM 105C OR AWM 2464 VW-1 ROHS (SEQ METERS) CE

* = Factory Code

B. Applicable Specifications

UL 1)

105°C / 300 V_{RMS} Component 1 AWM/STYLE 1569 a) AWM/STYLE 2464 80°C / 300 V_{RMS} Overall CM

105°C

VW-1

IEC EN 60332-1 Flame Behavior 2) EN 60332-2 Flame Behavior

CE: LVD 73/23/EEC Amendment 93/68/EEC

C. Environmental Compliance

1) EU Directive 2002/95/EC(RoHS):

All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.

2) REACH Regulation (EC 1907/2006):

This product does not contain any of the substances listed on the European Union REACH Substance of Very High Concern (SVHC) candidate list, dated 30 March 2010, in excess of a concentration of 0.1% weight/weight.

D. Physical & Mechanical Properties

1) Temperature Range -30 to 105°C Bend Radius 10X Cable Diameter 2) 269 Lbs, Maximum 3) Pull Tension

Sunlight Resistance 4) Yes

E. Electrical Properties (For Engineering purposes only)

1) Voltage Rating $300 V_{RMS}$

Capacitance 167.28 pf/m @1 kHz, Nominal Conductor to Conductor 2)

Ground Capacitance 301.76 pf/m @1 kHz, Nominal 3) 0.5904 µH/m, Nominal 4) Inductance

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE CUSTOMER PRODUCT SPECIFICATION

Part Number: B956204 Issue: 1
Page 2 of 2 Pages Issue Date: 9/7/2010
Effective Date: 11/2/2010

Conductor DCR 23.944 Ω/Km @20°C, Nominal 5.3792 Ω/Km @20°C, Nominal OA Shield DCR 6) F. Other Flange x Traverse x Barrel (inches) 1) Packaging 48 x 26 x 18 Continuous length 3280 FT a) 30 x 14 x 12 Continuous length 1640 FT b) 328 FT 16 x 11 x 8 Continuous length c) 164 FT 16 x 11 x 8 Continuous length d) [Spool dimensions may vary slightly]

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.