


Y WW = date code
 Y = year
 WW = week of manufacture



Electrical specification.

Turns ratio: 1:1


Impedance (ref. 1kHz):
 Primary: 800 ohms
 Secondaries: 800 ohms C.T.

Max. power: 2mW
 Frequency range: 200Hz - 15kHz

Inductance (nom.),
 measured at 100Hz, 0.27V:
 Primary: 1.7H
 Secondaries: (3 - 4): 420mH (3 - 5): 1.7H


DC resistance ()
 Primary: 63 - 85.8
 Secondary (centre tap): 42 - 55
 Secondary (total): 84 - 110

Isolation:
 Primary to secondary: 500VAC



Pin view

Hole dia. 1mm
 Tolerance on all hole positions ± 0.5mm



Walters Group Holdings Ltd.
 Unit 5, Oxonian Park, Langford Locks,
 Kidlington, Oxfordshire. OX5 1FP
 Tel: (01865) 855085 Fax: (01865) 855075
 Website: www.oep.co.uk

DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
Specification for E187A	1	13/02/04	CS		E187A
	3	15/06/04	CS		
	4	15/11/07	CS		
	5	27/08/09	CS		

Scale: 2 to 1

All dimensions in mm unless stated otherwise