


Interconnect Solutions



MKJ Series Connector




Since 1915, Cannon has been innovating circular connectors beginning with the first "Cannon Plugs." Over 90 years later, ICS continues this tradition with our new "Trinity" line of miniature circular connectors. With this innovative new product line, three truly is a magic number. Bringing a unique combination of Design, Functionality, and Flexibility, the Trinity product line excels in delivering a broad product line tailored directly to extensive VOC. In particular, this product demonstrates its robust design through the inclusion of specific, customer requested technologies including Pogo Pin contacts while delivery these technologies in a small, miniature circular form factor which provides substantial savings in both size and weight. Regarding functionality, Trinity again excels by providing various functional capabilities including threaded coupling, bayonet, and breakaway. Packaging these characteristics together, Trinity provides unparalleled functionality for numerous applications across multiple markets including Industrial, Medical, Aerospace, Military, and Space. Our Trinity product boldly positions itself as a primary resource to tackle your matrix of possibilities.

Product Features

- High contact density: size 23 contacts accommodate #22 - #28 wire and allowing 0.076 inch contact spacing
- Available with 3-85 rear release crimp or PCB contacts
- Master key with 2 secondary keys. 4 clocking positions available
- Significant weight and size reduction compared to traditional Mil Standard environmental connectors
- Available in jam nut, in-line, and square flange rear crimp receptacle versions. Jam nut and square flange PCB receptacle versions
- Rear accessory thread or integral band platform for direct attachment of cable shield or overmold
- Wire seal grommet for rear environmental sealing. Pin fluorosilicone interfacial seal provides interface sealing
- Available with double start threads allowing full mating in 1.5 turns
- Available with guick push/pull breakaway mechanism utilizing canted retention spring for guicker mating and demating
- Available with bayonet 1/4 turn locking mechanism
- Available with Pogo Pin technology utilizing ITT's unique spring probe pin/pad contact system

Applications

- Medical equipment: test and diagnostic
- Industrial equipment
- Commecial and militray aircraft electronics
- Unmanned aerial vehicles
- Missile systems
- Avionic systems
- Satellites
- Sensors
- Instrumentation
- Interconnections for helmets, weapons, battery packs, night vision goggles, aircraft headsets, etc.
- Navigation and Telemetry equipment
- Ruggedized computers and hand held communications equipment





The Challenge

ITT has a long history of providing standard and custom MIL-DTL-38999 connectors which meet the most stringent military requirements. ITT's major military and commercial accounts recently approached us requesting that we take our proven high reliability designs and shrink them to decrease weight and size while maintaining the connectors robust environmental performance and high reliability. Along with these requests, ICS received substantial commentary from other markets including Medical, Industrial, and Space, requesting a similar, miniature circular product.



The ITT Solution ...

ITT took on the challenge, driving innovation in mating capabilities and contacts to reduce size and weight while maintaining the high level of quality customers have come to expect from ITT over 90 years of engineering excellence. ITT collated a substantial amount of industry VOC from top tier military and commercial accounts. This feedback arrived from industry leading ICS customers, pioneering products in their fields including satellites & missiles, test and medical equipment, and tactical battlefield gear. Using this information and leveraging our historical product expertise, ITT engineered a product meeting our customers defined mix of Design, Functionality, and Flexibility. The result of this process represents our innovative new product line, Trinity. Offering three coupling methodologies {threaded, bayonet, and breakaway} and a highly engineered design, this innovative product reduces weight and size without sacrificing robust environmental performance or reliability. ITT ICS is proud to introduce our exciting new Trinity product line, engineered to the stringent quality standards for which ITT is world renown.




Design • Functionality • Flexibility



Technical overview

The Trinity MKJ family of mini circular connectors provide approximate electrical and mechanical characteristics of larger and heavier Military Standard Environmental connectors while reducing weight up to 71% and size up to 52%. All MKJ series connector's shells and jam nuts are available in high quality aluminum alloy or corrosion resistant steel per AMS-QQ-S 763. The MKJ series comes with rear accessory thread or integral band platform for direct attachment of cable shield and overmold. The MKJ series of connectors come with a variety of coupling mechanisms: threaded, breakaway, and bayonette. In addition, a Pogo Pin technology utilizing ITT's unique spring probe pin/touch pad contact system is available. The MKJ series receptacle comes with a variety of mounting options for both crimp and PCB contacts including in-line, jam nut, front mount, square flange mount, and flange mount. The MKJ0, MKJ1, and MKJ3 feature a master key and 2 secondary keys for positive mating with 4 clocking positions available. The MKJ0 connector is ideal for harsh shock and vibration environments. The MKJ3 connector can be fully mated in a ¹/₄ turn. The MKJ4 connector provides a quick push to mate / pull to unmate disconnect mechanism for fast breakaway connections.



Special Pogo Pin/Pad Connector. See factory for details.

	Series MKJ Performance			
Contact size / Spacing	#23 / 0.076 inches (1.9 mm)			
Contact Type	Rear Crimp or PCB Mount			
Wire Accomodation	#22 - #28 AWG			
Current Rating	5 Amps Maximum			
Voltage Rating	500 VAC RMS Sea Level			
Insulation Resistance	5000 Megaohms Minimum			
Operating Temperature	-55 degrees C to +150 degrees C			
Contact Resistance	8 Milliohms Maximum			
Vibration	20 g's in Accordance with MIL-STD-1344 Method 2005, Condition IV			
Shock	300 g's (MKJ1) 50 g's (MKJ0 and MKJ4) in Accordance with			
	MIL-STD-1344 Method 2004, Condition E			
EMI Shielding Effectiveness	40dB Attenuation, 100 MHz to 1000 MHz			
Coupling	Threaded, Quick Disconnect, Pogo Pin			
Coding	Master key and 2 secondary keys. 4 clocking positions available			
Housing material	Aluminum and Stainless Steel			
Layouts	31 layouts holding from 1 size 12 contact to 85 size 23 contacts			
Usage	Medical, Military, Commercial, and Industrial			
Receptacle Mounting	Jam Nut, Square Flange, In-line, PCB			





Electrical specifications for the connector

The MKJ series of products uses size 23 pin and socket contacts with equivalent electrical performance of size 22 contacts. These smaller contacts accept #22 - #28 AWG wire and allow the contact spacing to be reduced down to 0.076 inches. The connector's LCP dielectric insulating material can accommodate from 3 to 85 contacts in various shell sizes. This high density packaging, along with a reduced wall thickness and scoop, allows a dramatic decrease in size and weight of the MKJ connector while retaining the approximate mechanical and electrical characteristics of heavier and larger Military Standard Environmental connectors. The connector is capable of operating between -55 degrees Celsius and +150 degrees Celsius and can be mated up to 2,000 cycles. Maximum electrical current is 5 Amps and maximum voltage at sea level is 500 VAC RMS.

Max. Voltage 500 VAC RMS Sea Level		Max. Current	Operating	Temp	Durability	
		5 Amps Maximum	-55 degrees C to +	-55 degrees C to +150 degrees C		
J Product Lir	ne Talking Dog	МКЈ1 с	2 F	9-19	P N **	
MKJ1 MKJ3	 Threaded Coupling, Threaded Coupling, Bayonet Coupling Breakaway/Quick Dis Environmental Plug a 	Double Start ACME Thread sconnect and Receptacle with Banding/O and Receptacle with Threaded				
2 SHELL 1 - 2 - 6 - 7 -	STYLE In-Line Receptacle Square Flange Recep Straight Plug Jam Nut Receptacle	otacle				
FMATE C - F - W- Z - K - Y - T -	 F - Aluminum/Electroless Nickel W- Aluminum/OD Cad Z - Aluminum/Zinc Nickel, Black K - SS/Passivated Y - SS/Electroless Nickel, Black 			SHELL CLOCKING (POSITION) MKJ0 Series N - Normal X - Clocking Position X Y - Clocking Position Y Z - Clocking Position Z MKJ1 Series A - Normal 150° 210°		
5-3 6-1 6-4 6-7 7-1 8-13 9-4 9-19 10-26 12-2 12-37 13-2 13-37 14-55 15-55 16-55	13 Size 23 Contacts 4 Size 16 Contacts 19 Size 23 Contacts 2 Size 23 Contacts 2 Size 12 Contacts 37 Size 23 Contacts 37 Size 23 Contacts 37 Size 23 Contacts 55 Size 23 Contacts	Series MKJ0, MKJ1, MKJ2, M Series MKJ1 Series MKJ1 Series MKJ2, MKJ3, MKJ4 Series MKJ1	KJ3, MKJ4 KJ3, MKJ4	 B - Clocking Position B 75° 210° C - Clocking Position C 95° 230° D - Clocking Position D 140° 275° MKJ3 Series N - Normal 150° 210° X - Clocking Position X 75° 210° Y - Clocking Position Y 95° 230° Z - Clocking Position Z 140° 275° MKJ4 Series Omit for Single Key/Keyway A - Normal 150° 210° B - Clocking Position B 75° 210° C - Clocking Position C 95° 230° D - Clocking Position D 140° 275° 		

- S -Socket, Crimp, Removable
- Δ-Pin, PC Tail, .0.062 Extension
- Β-Pin, PC Tail, 0.109 Extension
- Socket, PC Tail, 0.062 Extension С-
- Socket, PC Tail, 0.109 Extension D -
- Pin, Pogo, Crimp, Removable G -
- Pad, Pogo, Crimp, Removable 0 -

(No modification code required for standard product) Consult Factor for other codes





Customer Support Locations

CHINA

Tuopandun Industrial Area, Jinda Cheng, Xiner Village, Shajing Town, Baoan District, Shenzhen City, Guangdong, China 518125 phone: +86.755.2726.7238 fax: +86.755.2726.7515

GERMANY

Cannonstrasse 1 Weinstadt, 71384 phone: +49.7151.699.0 fax: +49.7151.699.217

FRANCE

15, Boulevard Robert Thiboust Serris, France 77700 phone: +33.1.60.04.93.93 fax: +33.1.60.04.93.90

HONG KONG

Units 2405-6, 24/F, ING Tower 308 Des Voeux Road Central Hong Kong phone: +852.2732.2720 fax: +852.2732.2919

ITALY

Corso Europa 41/43 Lainate (MI), Italy 20020 phone: +39.02938721 fax: +39.0293872300

JAPAN

11-3, 5 Chome,Hibarigaoka, Zama-shi Kanagawa, Japan 228-0003 phone: +81.462.57.2010 fax: +81.462.57.1680

UK

Jays Close, Viables Estate Basingstoke, RG22 4BA phone: +44.1256.311200 fax: +44.1256.323356

USA

666 East Dyer Road Santa Ana, CA 92705 toll free: 1.800.854.3028 phone: +1.714.557.4700 fax: +1.714.628.2142