



**SAFETY DATA SHEET**  
**THERMALLY CONDUCTIVE EPOXY RESIN 2183A**

**1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING**

**PRODUCT NAME** THERMALLY CONDUCTIVE EPOXY RESIN 2183A  
**PRODUCT NO.** EER2183A  
**APPLICATION** Resin  
**SUPPLIER** ELECTROLUBE. A division of  
 HK WENTWORTH LTD  
 KINGSBURY PARK, MIDLAND  
 ROAD  
 SWADLINCOTE  
 DERBYSHIRE, DE11 0AN  
 UNITED KINGDOM  
 +44(0)1283 222 111  
 +44(0)1283 550 177  
 info@hkw.co.uk  
**EMERGENCY TELEPHONE** +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

**2 HAZARDS IDENTIFICATION**

Irritating to eyes and skin.

May cause sensitisation by skin contact.

Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**CLASSIFICATION** Xi;R36/38. R43. N;R50/53.

**3 COMPOSITION/INFORMATION ON INGREDIENTS**

Name	EC No.	CAS-No.	Content	Classification
ZINC OXIDE	215-222-5	1314-13-2	30-60%	N;R50/53
EPOXY RESIN (Number average MW <= 700 )	500-033-5	25068-38-6	10-30%	R43 Xi;R36/38 N;R51/53
NEOPENTYL GLYCOL DIGLYCIDYL ETHER	241-536-7	17557-23-2	10-30%	Xi;R38. R43.

The Full Text for all R-Phrases are Displayed in Section 16

**COMPOSITION COMMENTS**

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

**4 FIRST-AID MEASURES**

**NOTES TO THE PHYSICIAN**

Treat symptomatically

**INHALATION**

Move the exposed person to fresh air at once.

**INGESTION**

DO NOT INDUCE VOMITING! Get medical attention immediately! Rinse nose, mouth and throat with water.

**SKIN CONTACT**

Remove affected person from source of contamination. Rinse the skin immediately with lots of water. Get medical attention promptly if symptoms occur after washing.

**EYE CONTACT**

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention.

## THERMALLY CONDUCTIVE EPOXY RESIN 2183A

### 5 FIRE-FIGHTING MEASURES

#### EXTINGUISHING MEDIA

Fire can be extinguished using: Foam. Alcohol resistant foam. Dry chemicals, sand, dolomite etc.

#### SPECIAL FIRE FIGHTING PROCEDURES

Use water to keep fire exposed containers cool and disperse vapours.

### 6 ACCIDENTAL RELEASE MEASURES

#### SPILL CLEAN UP METHODS

Keep combustibles away from spilled material. Stop leak if possible without risk. DO NOT touch spilled material! Wear necessary protective equipment. Absorb in vermiculite, dry sand or earth and place into containers. Wash thoroughly after dealing with a spillage.

### 7 HANDLING AND STORAGE

#### USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Keep away from heat, sparks and open flame.

#### STORAGE PRECAUTIONS

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

### 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

#### INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

#### PROTECTIVE EQUIPMENT



#### ENGINEERING MEASURES

No specific ventilation requirements noted, except this product must not be used in a confined space without good ventilation.

#### RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit.

#### HAND PROTECTION

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

#### EYE PROTECTION

Wear approved, tight fitting safety glasses where splashing is probable.

#### OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of skin contact.

#### HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

### 9 PHYSICAL AND CHEMICAL PROPERTIES

#### APPEARANCE

Viscous Liquid

#### COLOUR

Grey

#### SOLUBILITY

Insoluble in water

#### RELATIVE DENSITY

2.16 @ 20C

#### VISCOSITY

80,000 mPas @ 20 C

### 10 STABILITY AND REACTIVITY

### THERMALLY CONDUCTIVE EPOXY RESIN 2183A

#### STABILITY

Stable under normal temperature conditions.

#### CONDITIONS TO AVOID

Avoid contact with acids and oxidising substances.

#### HAZARDOUS DECOMPOSITION PRODUCTS

Fire creates: Vapours/gases/fumes of: Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>). Nitrous gases (NO<sub>x</sub>).

### 11 TOXICOLOGICAL INFORMATION

#### INHALATION

May cause irritation to the respiratory system.

#### INGESTION

May cause discomfort if swallowed. May cause stomach pain or vomiting.

#### SKIN CONTACT

Irritating to skin. May cause sensitisation by skin contact. May cause allergic contact eczema. Prolonged contact may cause dryness of the skin. Acts as a defatting agent on skin. May cause cracking of skin, and eczema.

#### EYE CONTACT

Irritating to eyes. May cause chemical eye burns.

#### ROUTE OF ENTRY

Inhalation. Ingestion. Skin and/or eye contact.

<b>Name</b>	EPOXY RESIN (Number average MW <= 700 )
<b>Toxic Dose 1 - LD 50</b>	>5000 mg/kg (oral rat)
<b>Toxic Dose 2 - LD 50</b>	>20000 mg/kg (oral rat)
<b>Name</b>	NEOPENTYL GLYCOL DIGLYCIDYL ETHER
<b>Toxic Dose 1 - LD 50</b>	>2000 mg/kg (oral rat)

### 12 ECOLOGICAL INFORMATION

#### ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

<b>Name</b>	EPOXY RESIN (Number average MW <= 700 )
<b>LC 50, 96 Hrs, FISH mg/l</b>	3.1
<b>EC 50, 48 Hrs, DAPHNIA, mg/l</b>	1.4-1.7

### 13 DISPOSAL CONSIDERATIONS

#### DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

### 14 TRANSPORT INFORMATION



<b>UK ROAD CLASS</b>	9		
<b>PROPER SHIPPING NAME</b>	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (ZINC OXIDE, EPOXY RESIN (Number average MW <= 700 ))		
<b>UDF Phrase 1</b>	Class 9 Environmentally Hazardous substance		
<b>UN NO. ROAD</b>	3082	<b>UK ROAD PACK GR.</b>	III
<b>ADR CLASS NO.</b>	9	<b>ADR CLASS</b>	Class 9: Miscellaneous dangerous substances and articles.
<b>ADR PACK GROUP</b>	III	<b>HAZARD No. (ADR)</b>	90
<b>ADR LABEL NO.</b>	9	<b>HAZCHEM CODE</b>	3Z

**THERMALLY CONDUCTIVE EPOXY RESIN 2183A**

<b>CEFIC TEC(R) NO.</b>	90GM6-III	<b>RID CLASS NO.</b>	9
<b>RID PACK GROUP</b>	III	<b>UN NO. SEA</b>	3082
<b>IMDG CLASS</b>	9	<b>IMDG PACK GR.</b>	III
<b>EMS</b>	F-A, S-F	<b>MFAG</b>	See Guide
<b>MARINE POLLUTANT</b>	No.	<b>UN NO. AIR</b>	3082
<b>AIR CLASS</b>	9	<b>AIR PACK GR.</b>	III

**15 REGULATORY INFORMATION****SYMBOLS**

Irritant



Dangerous for the environment

**CONTAINS**

EPOXY RESIN (Number average MW <= 700 )  
NEOPENTYL GLYCOL DIGLYCIDYL ETHER

**RISK PHRASES**

R36/38 Irritating to eyes and skin.  
R43 May cause sensitisation by skin contact.  
R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

**SAFETY PHRASES**

S24/25 Avoid contact with skin and eyes.  
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.  
S37 Wear suitable gloves.  
S57 Use appropriate containment to avoid environmental contamination.  
S61 Avoid release to the environment. Refer to special instructions/safety data sheets.  
P5 Contains epoxy constituents. See information supplied by the manufacturer.

**UK REGULATORY REFERENCES**

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 1988.

**ENVIRONMENTAL LISTING**

Control of Pollution Act 1974. Control of Pollution (Special Waste Regulations) Act 1980. Rivers (Prevention of Pollution) Act 1961.

**EU DIRECTIVES**

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

**APPROVED CODE OF PRACTICE**

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

**GUIDANCE NOTES**

Workplace Exposure Limits EH40.

### THERMALLY CONDUCTIVE EPOXY RESIN 2183A

#### 16 OTHER INFORMATION

##### REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

##### ISSUED BY

Helen O'Reilly

**REVISION DATE** NOVEMBER 2008

**REV. NO./REPL. SDS** 3

**GENERATED**

**SDS NO.** 10868

##### RISK PHRASES IN FULL

R36/38 Irritating to eyes and skin.

R38 Irritating to skin.

R43 May cause sensitisation by skin contact.

R50/53 Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

#### DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.