





TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: PBT
 COLOR: BLACK
 CONTACT MATERIAL: COPPER ALLOY
 CONTACT TYPE: STAMPED
 CONTACT PLATING: GOLD
 QUALITY CLASS: 3 AS PER CECC 75 301-802
 PITCH: 2.54MM


ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 125°C
 FLAMABILITY RATING: UL94-V0
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 3A
 WORKING VOLTAGE: 250V AC
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC/MN
 CONTACT RESISTANCE: 20 mOHM MAX

SOLDERING
 WAVE PROCESS ONLY

PACKAGING
 BAG

DIMENSION
 A = 2.54 x (NB. PIN / 2 - 1)
 B = 2.54x (NB. PIN / 2)

RoHS Compliant							SIZE	
G	12-JUL-10	UPDATE	JC	PROJECTION: 	GENERAL TOLERANCE			
F	08-JUL-10	PACKAGING	JC		.X = +/- 0.2			
E	23-NOV-07	MODIFICATIONS	EC		.XX = +/- 0.15			
D	07-DEC-06	DRAW	EC					
C	29-MAR-04	LEAD FREE	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: 2.54MM ANGLED DUAL PIN HEADER	A4	
B	15-MAR-04		JP		SCALE:			
A	03-MAY-99	PDF	JP		SHEET: 1/2	WERI PART NO: 6130xx 21021		
REV	DATE	FILE	BY		DRAW: PEARL			

