


Dimensions:

(ANSI / IEC Standards)



DIMENSIONS	
MM	INCHES
1.8	0.071
2.0	0.079
12.0	0.472
15.7	0.618
16.0	0.630

Engineering Data:

Cell Chemistry:	Lithium/Manganese Dioxide (CR)
Designation:	ANSI/NEDA-5009LC, IEC-CR1620
Nominal Voltage:	3.0 V
Maximum off-load voltage:	3.7 V
Approximate Weight:	1.3 g.
Approximate Volume:	.41 CU CM
Nominal Capacity:	75mAh (47k Ohm Cont. to 2.0V @ 20°C)
Operating Temp. Range:	-30°C to 60°C
Storage Temp. Range:	-20°C to 45°C
Storage Loss @ 20°C:	Less than .3% per year

Typical Service (@ 20°C):

Application:	Load	Load Unit	Duty Cycle	Daily Cycle	EPV	ANSI Min. Ave. Duration	Actual
Rating:	47	kOhms		24 h	2.0	1150 Hours	1350 Hours

Environmental: Meets Environmental Protection Agency (EPA) Requirements for landfill disposal. No Mercury Added Formulation.