Product data sheet Characteristics

XS108B3PAM8

inductive sensor XS1 M8 - L42mm - brass - Sn2mm - 12..24VDC - M8

Main

| Sensor type Ir Product specific application - | Seneral purpose inductive proximity sensor S1 Sylindrical M8 |
|---|---|
| Product specific application - | S1 Sylindrical M8 |
| cation | ylindrical M8 |
| Sensor name X | ylindrical M8 |
| | • |
| Sensor design C | 2 mm |
| Size 4 | |
| Body type F | ixed |
| Detector flush mounting F acceptance | lush mountable |
| Material N | letal |
| Type of output signal D | iscrete |
| Wiring technique 3 | -wire |
| [Sd] sensing range > | 02.5 mm |
| [Sn] nominal sensing 2 distance | .5 mm |
| Discrete output function 1 | NO |
| Output circuit type D | C |
| Discrete output type P | NP |
| Electrical connection N | 18 male connector, 3 pins |
| [Us] rated supply voltage | 224 V DC with reverse polarity protection |
| Switching capacity in < mA | = 200 mA with overload and short-circuit protection |
| | P65 conforming to IEC 60529 P67 conforming to IEC 60529 |
| Sale per indivisible 1 quantity | |

Complementary

| o impromortary | |
|-----------------------|---------------------------------|
| ISO thread | M8 x 1 |
| Detection face | Frontal |
| Enclosure material | Nickel plated brass |
| Operating zone | 02 mm |
| Differential travel | 115% of Sr |
| Status LED | 1 LED (yellow) for output state |
| Supply voltage limits | 1036 V DC |
| Switching frequency | <= 2500 Hz |
| Voltage drop | <= 2 V (closed state) |
| Current consumption | <= 10 mA (no-load) |
| Delay first up | <= 10 ms |
| Delay response | <= 0.2 ms |
| Delay recovery | <= 0.2 ms |
| Marking | CE |
| Threaded length | 26 mm |
| Length | 42 mm |
| Product weight | 0.03 kg |
| | |

Environment

| Product certifications | CSA UL |
|---------------------------------------|--|
| Ambient air temperature for operation | -2570 °C |
| Ambient air temperature for storage | -4085 °C |
| Vibration resistance | 25 gn, amplitude: +/- 2 mm (f = 1055 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn (duration = 11 ms) conforming to IEC 60068-2-27 |
| RoHS EUR status | Compliant |
| RoHS EUR conformity date | 1104 |

