

XS7C40DP210

inductive sensor XS7 40x40x117 - plastic -
Sn15mm - 12..48VDC - terminals



Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XS7
Sensor design	Form 40 x 40 x 117
Size	117 mm
Body type	Fixed
Detector flush mounting acceptance	Flush mountable
Material	Plastic
Enclosure material	Plastic
Type of output signal	Discrete
Wiring technique	2-wire
[Sd] sensing range	> 8...15 mm
[Sn] nominal sensing distance	15 mm
Discrete output function	1 NO or 1 NC programmable
Output circuit type	DC
Electrical connection	Screw-clamp terminals, clamping capacity: 2 x 1.5 mm ²
[Us] rated supply voltage	12...48 V DC with reverse polarity protection
Switching capacity in mA	1.5...100 mA with overload and short-circuit protection
IP degree of protection	IP67 conforming to IEC 60529

Complementary

Detection face	5 positions turret head
Operating zone	0...12 mm
Differential travel	3...20% of Sr
Repeat accuracy	<= 3% of Sr
Cable entry	1 entry tapped for Pg 13.5 cable gland
Status LED	1 LED yellow for output state
Supply voltage limits	10...58 V DC
Residual current	<= 0.5 mA for open state
Switching frequency	<= 1500 Hz
Voltage drop	<= 4 V at closed state
Delay first up	<= 5 ms
Delay response	<= 2 ms
Delay recovery	<= 5 ms
Marking	CE
Height	117 mm
Width	40 mm
CAD overall height	117 mm
CAD overall depth	41 mm
Product weight	0.22 kg

Environment

Product certifications	CCC CSA C-Tick UL
Ambient air temperature for operation	-25...70 °C
RoHS EUR status	Compliant
RoHS EUR conformity date	0836