





Compliance with RoHS Directive

FEATURES

1. Compact with high contact rating Even with small 10 mm .394 inch (H) x 11 mm .433 inch (W) x 20 mm .787 inch (L) (dimensions, high capacity switching is provided: 1a, 8 A 250 V AC; 2a and 1a1b, 5 A 250 V AC.

2. High switching capability

High contact pressure, low contact bounce, and wiping operation improve resistance to weld bonding. Resistant against lamp load and dielectric loading: 1a achieves maximum switching capacity of 2,000 VA (8A 250 V AC).

1a 8A, 1a1b/2a 5A small polarized power relays

3. High sensitivity

Using the same type of highperformance polar magnetic circuits as DS relays, by matching the spring load to the magnetic force of attraction, greater sensitivity has been achieved. The resultant pick up sensitivity of about 190 mW makes possible direct driving of transistors and chips.

4. High breakdown voltage

Breakdown voltage has been raised by keeping the coil and contacts separate.

Between contact and coil	Between contacts			
3,000 Vrms for 1 min. 5,000 V surge breakdown voltage	1,000 Vrms for 1 min. 1,500 V surge breakdown voltage			
Conforms with FCC Part 68				

5. Latching types available

6. Wide variation

Three types of contact arrangement are offered: 1a, 2a, and 1a1b. In addition, each is available in standard and reversed polarity types.


- 7. Sealed construction allows automatic washing.
- 8. Complies with safety standards Complies with Japan Electrical Appliance and Material Safety Law requirements for operating 200 V power supply circuits, and complies with UL, CSA, and TÜV safety standards.
- 9. Sockets are available.

DSP RELAYS

TYPICAL APPLICATIONS

- 1. Office and industrial electronic devices
- 2. Terminal devices of information processing equipment, such as printer, data recorder.
- 3. Office equipment (copier, facsimile)
- 4. Measuring instruments
- 5. NC machines, temperature controllers and programmable logic controllers.

ORDERING INFORMATION



Notes: 1. Reverse polarity types available (add suffix-R) 2. Certified by UL, CSA and TÜV

TYPES

Contact	Nominal coil	Single side stable	2 coil latching
arrangement	voltage	Part No.	Part No.
	3V DC	DSP1a-DC3V	DSP1a-L2-DC3V
	5V DC	DSP1a-DC5V	DSP1a-L2-DC5V
	6V DC	DSP1a-DC6V	DSP1a-L2-DC6V
1 Form A	9V DC	DSP1a-DC9V	DSP1a-L2-DC9V
	12V DC	DSP1a-DC12V	DSP1a-L2-DC12V
	24V DC	DSP1a-DC24V	DSP1a-L2-DC24V
1 Form A 1 Form B	3V DC	DSP1-DC3V-F	DSP1-L2-DC3V-F
	5V DC	DSP1-DC5V-F	DSP1-L2-DC5V-F
	6V DC	DSP1-DC6V-F	DSP1-L2-DC6V-F
	9V DC	DSP1-DC9V-F	DSP1-L2-DC9V-F
	12V DC	DSP1-DC12V-F	DSP1-L2-DC12V-F
	24V DC	DSP1-DC24V-F	DSP1-L2-DC24V-F
	3V DC	DSP2a-DC3V	DSP2a-L2-DC3V
	5V DC	DSP2a-DC5V	DSP2a-L2-DC5V
	6V DC	DSP2a-DC6V	DSP2a-L2-DC6V
2 Form A	9V DC	DSP2a-DC9V	DSP2a-L2-DC9V
	12V DC	DSP2a-DC12V	DSP2a-L2-DC12V
	24V DC	DSP2a-DC24V	DSP2a-L2-DC24V

Standard packing: Carton: 50 pcs.; Case: 500 pcs. Note: Reverse polarity type are manufactured by lot upon receipt of order. Self-clinching types are also available, please consult us.

* For sockets, see page 111.

RATING

1. Coil data

1) Single side stable

Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power	Max. applied voltage (at 20°C 68°F)
3V DC			100mA	30Ω		
5V DC			60mA	83Ω	20014/	130%V of
6V DC	80%V or less of	al voltage nominal voltage	50mA	120Ω		
9V DC	(Initial)		33.3mA	270Ω	300mW	nominal voltage
12V DC		(initial)	25mA	480Ω		
24V DC			12.5mA	1,920Ω		

2) 2 coil latching

Nominal coil voltage	Set voltage (at 20°C 68°F)	Reset voltage (at 20°C 68°F)	cur	operating rent 20°C 68°F)		sistance 20°C 68°F)		operating wer	Max. applied voltage (at 20°C 68°F)
Ū			Set coil	Reset coil	Set coil	Reset coil	Set coil	Reset coil	
3V DC			100mA	100mA	30Ω	30Ω			
5V DC			60mA	60mA	83Ω	83Ω	120Ω 270Ω 300mW 300r	300mW	N 130%V of nominal voltage
6V DC	80%V or less of nominal voltage	80%V or less of	50mA	50mA	120Ω	120Ω			
9V DC	(Initial)	nominal voltage (Initial)	33.3mA	33.3mA	270Ω	270Ω		3001111	
12V DC	((25mA	25mA	480Ω	480Ω			
24V DC			12.5mA	12.5mA	1,920Ω	1,920Ω			


Characteristics		Item	Specifications					
	Arrangement		1 Form A	1 Form A 1 Form B	2 Form A			
Contact	Contact resistance (I	nitial)	Max. 30 mΩ (By voltage drop 6 V DC 1A)					
	Contact material		Au-flashed AgSnO ₂ type					
	Nominal switching ca	apacity (resistive load)	8 A 250 V AC, 5A 30V DC	8 A 250 V AC, 5A 30V DC 5 A 250 V AC, 5 A 30 V DC				
	Max. switching powe	r (resistive load)	2,000 VA, 150 W	2,000 VA, 150 W 1,250 VA, 150 W				
Poting	Max. switching voltage	je	250 V AC, 30 V DC					
Rating	Max. switching curre	nt	8 A AC, 5 A DC	5 A A	C, DC			
	Nominal operating po	ower		300 mW				
	Min. switching capac	ity (Reference value)*1		10m A 5 V DC				
	Insulation resistance	(Initial)	Min. 1,000MΩ (at 500V DC) M	easurement at same location as	s "Breakdown voltage" section.			
		Between open contacts	1,000 Vr	ms for 1min. (Detection current	: 10mA.)			
	Breakdown voltage (Initial)	Between contact sets	2,000 Vrms (1 Form A 1 Form B, 2 Form A) (Detection current: 10mA.)					
_	(miliar)	Between contact and coil	3,000 Vrms for 1min. (Detection current: 10mA.)					
	Surge breakdown voltage*2	between contacts and coil	5,000 V					
	Temperature rise (co	il) (at 65°C 149°F)	Max. 55°C	Max. 40°C	Max. 55°C			
	Operate time [Set tin	ne] (at 20°C 68°F)	Max. 10 ms [10 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.)					
	Release time [Reset time] (at 20°C 68°F)		Max. 5 ms [10 ms] (Nominal c	Max. 5 ms [10 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.) (without diode)				
	Shock resistance	Functional	Min. 196 m/s ² (Half-wave pulse of sine wave: 11 ms; d		detection time: 10µs.)			
Mechanical	Shock resistance	Destructive	Min. 980 n	n/s ² (Half-wave pulse of sine wa	ve: 6 ms.)			
characteristics	Vibration resistance	Functional	10 to 55 Hz at do	ouble amplitude of 2 mm (Detec	tion time: 10μs.)			
	VIDIATION TESISTANCE	Destructive	10 to 55 Hz at double amplitude of 3.5 mm					
Expected life	Mechanical			Min. 5×107 (at 180 times/min.)				
Expected life	Electrical			Min. 10 ⁵ (resistive load)				
Conditions for operation, transpo (Not freezing and condensing at			-40°C to +60°C -40°C to +65°C -40		Ambient temperature: -40°C to +60°C -40°F to +140°F			
Conditions	Solder heating			⁻ (10s), 300°C 572°F (5s), 350° oldering depth: 2/3 terminal pitc				
	Max. operating spee	d		3 cps				
Unit weight			Approx. 4.5 g .16 oz					

Notes: *1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.


*2. Wave is standard shock voltage of $\pm 1.2\times 50\mu s$ according to JEC-212-1981


*3. The upper limit of the ambient temperature is the maximum temperature that can satisfy the coil temperature rise value. Refer to Usage, transport and storage conditions in NOTES.


REFERENCE DATA




3.-(1) Coil temperature rise (1 Form A) Tested sample: DSP1a-DC12V, 5 pcs.

















All Rights Reserved © COPYRIGHT Panasonic Electric Works Co., Ltd.

100


Coil applied voltage, %V

120

80


4.-(1) Operate & release time (without diode, 1 Form A) Tested sample: DSP1a-DC12V, 5 pcs. ms Operate & release time, Operate time Release time Max. 80 120 100 Coil applied voltage, %V

4.-(4) Operate & release time (with diode, 1 Form A) Tested sample: DSP1a-DC12V, 5 pcs.




5.-(1) Change of pick-up and drop-out voltage (1 Form A)

Tested sample: DSP1a-DC12V, 5 pcs.




6.-(1) Influence of adjacent mounting (1 Form A)







4.-(2) Operate & release time (without diode, 1 Form A 1 Form B) Tested sample: DSP1-DC12V, 5 pcs.




4.-(5) Operate & release time (with diode, 1 Form A 1 Form B) Tested sample: DSP1-DC12V, 5 pcs.




5.-(2) Change of pick-up and drop-out voltage (1 Form A 1 Form B) Tested sample: DSP1-DC12V, 5 pcs.




6.-(2) Influence of adjacent mounting (1 Form A 1 Form B) Tested sample: DSP1-DC12V, 5 pcs.




4.-(3) Operate & release time (without diode, 2 Form A) Tested sample: DSP2a-DC12V, 5 pcs.)




4.-(6) Operate & release time (with diode, 2 Form A) Tested sample: DSP2a-DC12V, 5 pcs.






Tested sample: DSP2a-DC12V, 5 pcs.



6.-(3) Influence of adjacent mounting (2 Form A)


Tested sample: DSP2a-DC12V, 5 pcs.





All Rights Reserved © COPYRIGHT Panasonic Electric Works Co., Ltd.

DIMENSIONS (mm inch) The CAD data of the products with a CAD Data mark can be downloaded from: http://panasonic-electric-works.net/ac 1.1 Form A type External dimensions PC board pattern (Bottom view) CAD Data 2 coil latching Single side stable Single side stable **4-1.2 dia** 4-.047 d 20.2 20.2 11.0 2.54










3.2 Form A type CAD Data



Single side stable 2 coil latching 20.2 .795 20.2 11.0 10.0 10.5 10.0 10.5 .394 413 ŧ 0.3 0.3 3.5 3.5 .138 0.8 0.8 0.8 0.8 1.21 7.62 -7.62 **-7.62** _10.16 -7.62 2.54

External dimensions

General tolerance: ±0.3 ±.012



SAFETY STANDARDS

Item -		UL/C-UL (Recognized)		CSA (Certified)		TÜV (Certified)	
	File No.	Contact rating	File No.	Contact rating	File No.	Rating	
1 Form A	E43028	8A 250V AC ¼HP 125, 250V AC 5A 30V DC	LR26550 etc.	8A 250V AC ¼HP 125, 250V AC 5A 30V DC	B 02 10 13461 238	8A 250V AC (cosφ=1.0) 5A 250V AC (cosφ=0.4) 5A 30V DC	
1 Form A 1 Form B	E43028	5A 250V AC ¼6HP 125, 250V AC 5A 30V DC	LR26550 etc.	5A 250V AC ¼HP 125, 250V AC 5A 30V DC	B 02 10 13461 238	5A 250V AC (cosφ=1.0) 3A 250V AC (cosφ=0.4) 5A 30V DC	
2 Form A	E43028	5A 250V AC ¼0HP 125, 250V AC 5A 30V DC	LR26550 etc.	5A 250V AC ¼0HP 125, 250V AC 5A 30V DC	B 02 10 13461 238	5A 250V AC (cosφ=1.0) 3A 250V AC (cosφ=0.4) 5A 30V DC	

* Remarks: The standard certified for may differ depending on where the product was manufactured.

NOTES

1. Soldering conditions

Please obey the following conditions when soldering automatically. 1) Preheating: Within 120°C 248°F and

within 120 seconds 2) Soldering iron: 260°C±5°C 500°F±41°F and within 6 seconds

2. Cleaning

For automatic cleaning, the boiling method is recommended. Avoid ultrasonic cleaning which subjects the relays to high frequency vibrations, which may cause the contacts to stick. It is recommended that a fluorinated hydrocarbon or other alcoholic solvents be used.

For Cautions for Use.

3. External magnetic field

Since DY relays are highly sensitive polarized relays, their characteristics will be affected by a strong external magnetic field. Avoid using the relay under that condition.

4. Coil operating power

Pure DC current should be applied to the coil. The wave form should be rectangular. If it includes ripple, the ripple factor should be less than 5%. However, check it with the actual circuit since the characteristics may be slightly different. 5. When using, please be aware that the a contact and b contact sides of 1 Form A and 1 Form B types may go on simultaneously at operate time and release time.



ACCESSORIES





Compliance with RoHS Directive

TYPES AND APPLICABLE RELAYS


	Type No.	For DSP1a		For DSP1a, DSP1, DSP2a		
Applicable relays		DSP1a-PS	DSP1a-PSL2	DSP2a-PS	DSP2a-PSL2	
DSP1a relays		OK	OK	OK	OK	
DSP1a-L2 relays			OK		OK	
DSP1 relays				OK	OK	
DSP1-L2 relays					OK	
DSP2a relays				OK	OK	
DSP2a-L2 relays					OK	


SPECIFICATIONS

Item	Specifications			
Breakdown voltage	3,000 Vrms between terminals (Except for the portion between coil terminals)			
Insulation resistance	1,000 MΩ between terminals at 500 V			
Heat resistance	150°C for 1 hour			
Max. continuous current	8 A			

DIMENSIONS (mm inch)


The CAD data of the products with a CAD Data mark can be downloaded from: http://panasonic-electric-works.net/ac





Terminal No.2 and 15 are for DSP1a-PSL2 only.

PC board pattern (Bottom view) 2 DSP2a-PS, DSP2a-PSL2




Terminal No.2 and 15 are for DSP2a-PSL2 only.

FIXING AND REMOVAL METHOD

1. Match the direction of relay and socket.



2. Both ends of relays are fixed so tightly that the socket hooks on the top surface of relays.




Good

No good

3. Remove the relay, applying force in the direction shown below.



4. In case there is not enough space for finger to pick relay up, use screw drivers in the way shown below.



Notes: 1. Exercise care when removing relays. If greater than necessary force is applied at the socket hooks, deformation may alter the dimensions so that the hook will no longer catch, and other damage may also occur.
2. It is hazardous to use IC chip sockets.