

### 2.3x7mm RECTANGULAR SOLID LAMP

PRELIMINARY SPEC

Part Number: L-153GDT

**GREEN** 

PAGE: 1 OF 3


### **Features**

- LOW POWER CONSUMPTION.
- RELIABLE AND RUGGED.
- EXCELLENT UNIFORMITY OF LIGHT OUTPUT.
- SUITABLE FOR LEVEL INDICATOR.
- I.C. COMPATIBLE.
- LONG LIFE SOLID STATE RELIABILITY.
- RoHS COMPLIANT.

### **Description**

The Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

# **Package Dimensions**



- Notes:
  1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.25(0.01") unless otherwise noted.

  3. Lead spacing is measured where the leads emerge from the package.
- 4. Specifications are subject to change without notice.

SPEC NO: DSAC2941 **REV NO: V.4 DATE: JUL/18/2006** APPROVED: J. Lu CHECKED: Allen Liu DRAWN: W.J.ZHU

# Kingbright

## Selection Guide

Part No.	Dice	Lens Type	lv (mcd) [2] @ 10mA		Viewing Angle [1]
			Min.	Тур.	201/2
L-153GDT	GREEN (GaP)	GREEN DIFFUSED	0.7	3	110°

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.
  2. Luminous Intensity / Luminous Flux: +/-15%.

## Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Green	565		nm	IF=20mA
λD [1]	Dominant Wavelength	Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Green	30		nm	IF=20mA
С	Capacitance	Green	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Green	2.2	2.5	V	IF=20mA
lR	Reverse Current	Green		10	uA	VR = 5V

- 1. Wavelength: +/-1nm.
- 2. Forward Voltage: +/-0.1V.

# Absolute Maximum Ratings at Ta=25°C


Parameter	Green	Units
Power dissipation	105	mW
DC Forward Current	25	mA
Peak Forward Current [1]	140	mA
Reverse Voltage	5	V
Operating/Storage Temperature	-40°C To +85°C	
Lead Solder Temperature [2] 260°C For 3 Seconds		
Lead Solder Temperature [3]	260°C For 5 Seconds	

### Notes:

- 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- 2. 2mm below package base.
- 3. 5mm below package base.

SPEC NO: DSAC2941 **REV NO: V.4** DATE: JUL/18/2006 PAGE: 2 OF 3 APPROVED: J. Lu CHECKED: Allen Liu DRAWN: W.J.ZHU

# Kingbright



SPEC NO: DSAC2941 REV NO: V.4 DATE: JUL/18/2006 PAGE: 3 OF 3
APPROVED: J. Lu CHECKED: Allen Liu DRAWN: W.J.ZHU