


## Isoprobe® II Safety Oscilloscope Probes





Fully insulated, high frequency oscilloscope probes. Supplied with plug-in reference lead

- Highly flexible coaxial cable
- Insulated safety BNC plugs
- Ergonomically designed probes with finger guards and stainless steel tips
- Up to 1000V CATII IEC1010 rating

UL

Typ / Type	Isoprobe® II - 100:1	
Teilungsverhältnis / Dividing ratio / Rapport	100:1	
Eingangskapazität / Input capacitance / Capacité d'entrée	6,5 pF	
Kompensationsbereich / Compensation range / Plage de compensation (werkseitige Einstellung / works setting / réglage en usine)	10 pF ... 25 pF (15 pF)	
Eingangswiderstand / Input impedance / Résistance d'entrée	100 MΩ	
Frequenzbereich / Frequency range / Plage de fréquences	0 ... 300 MHz	
Anstiegszeit / Rise time / Temps de montée	< 1 ns	
Leitungslänge / Lead length / Longueur du câble	120 cm	
Bemessungsspannung (frequenzabhängig) Rated voltage (frequency-dependent) Tension assignée (fonction de la fréquence)	1000 V, CAT II (600 V, CAT III) (Max. 5 kV <sub>Spitze</sub> / kV <sub>Peak</sub> / kV <sub>crête</sub> )	





**RZ 043**