

4-Channel Analog Input Module ±10 V/0-10 V

Single-ended (S.E.)











Fig. 750 Series/Technical data see page 24/Delivered without miniature WSB markers
750/753 Series marking see pages 12 ... 13 / 14 ... 15

The analog input module receives signals with the standardized values ±10V and 0-10V.

The input signal is electrically isolated and will be transmitted with a resolution of 12 bits.

The internal system supply is used for the power supply of the module.

The input channels of a module have one common ground potential.

Description	Item No.	Pack. Unit
4AI ±10V DC S.E.	750-457	10 ¹⁾
4AI ±10V DC S.E./T	750-457/025-000	1
(Operating temperature -20 °C ... +60 °C)		
4AI 0-10V DC S.E.	750-459	10 ¹⁾
4AI ±10V DC S.E. (without connector)	753-457	10 ¹⁾
4AI 0-10V DC S.E. (without connector)	753-459	10 ¹⁾
1) Also available individually		
Accessories	Item No.	Pack. Unit
 753 Series Connectors	753-110	25
 Coding elements	753-150	100
Miniature WSB Quick marking system		
 plain	248-501	5
 with marking	see pages 304 ... 305	
Approvals		
750 and 753 Series		
Conformity marking	CE	
 UL 508		
 ANSI/ISA 12.12.01	Class I, Div. 2, Grp. ABCD, T4	
750 Series		
 EN 60079-15	I M2 / II 3 GD Ex nA IIC T4	
Shipbuilding	see "Approvals Overview" in section 1	

Technical Data	
Number of inputs	4
Voltage supply	via system voltage DC/DC
Current consumption (internal)	65 mA
Input voltage (max.)	± 40 V
Signal voltage	± 10 V (750-457, 753-457) 0 V ... 10 V (750-459, 753-459)
Input resistance	> 100 kΩ
Resolution	12 bits
Conversion time (typ.)	10 ms
Measuring error (25 °C)	< ± 0.2 % of the full scale value
Temperature coefficient	< ± 0.01 % / K of the full scale value
Isolation	500 V system/supply
Bit width	4 x 16 bits data 4 x 8 bits control/status (optional)
Wire connection	CAGE CLAMP®
Cross sections	0.08 mm² ... 2.5 mm² / AWG 28 ... 14
Stripped lengths, 750/753 Series	8 ... 9 mm / 0.33 in 9 ... 10 mm / 0.37 in
Width	12 mm
Weight	51 g
EMC CE-Immunity to interference	acc. to EN 61000-6-2 (2005)
EMC CE-Emission of interference	acc. to EN 61000-6-4 (2007)
EMC marine applications - Immunity to interference	acc. to Germanischer Lloyd (2003)
EMC marine applications - Emission of interference	acc. to Germanischer Lloyd (2003)