



SAFETY DATA SHEET ISOPROPANOL CLEANING FLUID

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME ISOPROPANOL CLEANING FLUID
PRODUCT NO. IPA-b
EIPA01L
EIPA05L
ZE
APPLICATION Cleaning Product
SUPPLIER ELECTROLUBE. A division of
HK WENTWORTH LTD
ASHBY PARK, COALFIELD
WAY,
ASHBY DE LA ZOUCH,
LEICESTERSHIRE LE65 1JF
UNITED KINGDOM
+44 (0)1530 419600
+44 (0)1530 416640
info@hkw.co.uk
EMERGENCY TELEPHONE +44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

2 HAZARDS IDENTIFICATION

Highly flammable.
Vapours may cause drowsiness and dizziness.
Irritating to eyes.
CLASSIFICATION (67/548) Xi;R36. F;R11. R67.

PHYSICAL AND CHEMICAL HAZARDS

The product is highly flammable, and explosive vapours/air mixtures may be formed even at normal room temperatures.

HUMAN HEALTH

See section 11 for additional information on health hazards.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548/EEC)
PROPAN-2-OL	200-661-7	67-63-0	80-100%	F;R11 Xi;R36 R67

The Full Text for all R-Phrases is Displayed in Section 16

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

No recommendation given, but first aid may still be required in case of accidental exposure, inhalation or ingestion of this chemical. If in doubt, GET MEDICAL ATTENTION PROMPTLY! Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

INGESTION

Provide rest, warmth and fresh air. Immediately rinse mouth and drink plenty of water (200-300 ml). Get medical attention. DO NOT INDUCE VOMITING!

SKIN CONTACT

Remove contaminated clothing immediately and wash skin with soap and water. Get medical attention if irritation persists after washing.

ISOPROPANOL CLEANING FLUID

EYE CONTACT

Promptly wash eyes with plenty of water while lifting the eye lids. Make sure to remove any contact lenses from the eyes before rinsing. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog.

SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk. Use water to keep fire exposed containers cool and disperse vapours. Dike and collect extinguishing water.

SPECIFIC HAZARDS

Oxides of: Carbon.

PROTECTIVE MEASURES IN FIRE

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

6 ACCIDENTAL RELEASE MEASURES

PERSONAL PRECAUTIONS

Follow precautions for safe handling described in this safety data sheet. Do not smoke, use open fire or other sources of ignition. Take precautionary measures against static discharges. Provide adequate ventilation.

ENVIRONMENTAL PRECAUTIONS

Spillages or uncontrolled discharges into watercourses must be IMMEDIATELY alerted to the Environmental Agency or other appropriate regulatory body.

SPILL CLEAN UP METHODS

Absorb with inert, damp, non-combustible material, then flush area with water. Collect spillage in containers, seal securely and deliver for disposal according to local regulations.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Avoid spilling, skin and eye contact. Keep away from heat, sparks and open flame. Avoid inhalation of vapours and spray mists. Provide good ventilation.

STORAGE PRECAUTIONS

Flammable/combustible - Keep away from oxidisers, heat and flames. Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

STORAGE CLASS

Flammable liquid storage.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
PROPAN-2-OL	WEL	400 ppm	999 mg/m ³	500 ppm	1250 mg/m ³	

WEL = Workplace Exposure Limit.

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT



ENGINEERING MEASURES

Provide adequate ventilation. Observe occupational exposure limits and minimize the risk of inhalation of vapours.

RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit.

ISOPROPANOL CLEANING FLUID

HAND PROTECTION

Use protective gloves. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Butyl rubber gloves are recommended.

EYE PROTECTION

Wear approved, tight fitting safety glasses where splashing is probable.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. When using do not eat, drink or smoke. Eating, smoking and water fountains prohibited in immediate work area.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid
COLOUR	Colourless
ODOUR	Odour of alcohol
MOL. WEIGHT	60.10 g/mol
BOILING POINT (°C)	82 C (179.6 F)
RELATIVE DENSITY	0.790 @ 20 °c (68 F)
VAPOUR DENSITY (air=1)	2.8
VAPOUR PRESSURE	4.16 kPa @ 20 °c (68 F)
EVAPORATION RATE	2.93
VISCOSITY	3.06 cSt @ 20 °c (68 F)
FLASH POINT (°C)	12 C (53.6 F) CC (Closed cup).
AUTO IGNITION TEMPERATURE (°C)	399 (750,2 F)
FLAMMABILITY LIMIT - LOWER(%)	2.50
FLAMMABILITY LIMIT - UPPER(%)	12.70

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions and recommended use.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid excessive heat for prolonged periods of time. Avoid contact with acids and oxidising substances.

HAZARDOUS POLYMERISATION

Will not polymerise.

MATERIALS TO AVOID

Strong oxidising substances. Strong acids.

HAZARDOUS DECOMPOSITION PRODUCTS

Oxides of: Carbon.

11 TOXICOLOGICAL INFORMATION

INHALATION

May cause irritation to the respiratory system. Vapours may cause drowsiness and dizziness.

INGESTION

May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.

SKIN CONTACT

Irritating to skin. Prolonged contact may cause dryness of the skin. Acts as a defatting agent on skin. May cause cracking of skin, and eczema.

EYE CONTACT

Irritating to eyes.

ROUTE OF ENTRY

Skin absorption. Ingestion. Skin and/or eye contact.

TARGET ORGANS

Central nervous system Eyes Respiratory system, lungs Skin

ISOPROPANOL CLEANING FLUID

MEDICAL SYMPTOMS

Irritation of eyes and mucous membranes. Dilated pupils. Rhinitis (inflammation of the nasal mucous membranes). Upper respiratory irritation. General respiratory distress, unproductive cough. Skin irritation. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo.

Name PROPAN-2-OL

12 ECOLOGICAL INFORMATION

ECOTOXICITY

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

MOBILITY

The product is soluble in water.

BIOACCUMULATION

The product is not bioaccumulating.

DEGRADABILITY

The product is biodegradable.

ACUTE FISH TOXICITY

Not considered toxic to fish.

Name PROPAN-2-OL

13 DISPOSAL CONSIDERATIONS

GENERAL INFORMATION

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority. Do not puncture or incinerate even when empty. Rags and the like, moistened with flammable liquids, must be discarded into designated fireproof bucket.

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION

GENERAL

For US Domestic transportation this product is classified as a Consumer Commodity. For International transportation this product is classified as UN1219 ISOPROPANOL (ISOPROPYL ALCOHOL)



PROPER SHIPPING NAME ISOPROPANOL (ISOPROPYL ALCOHOL)

PROPER SHIPPING NAME CONSUMER COMMODITY

ENVIRONMENTALLY HAZARDOUS SUBSTANCE/MARINE POLLUTANT No.

UN NO. ROAD 1219

ADR CLASS NO. 3

ADR CLASS Class 3: Flammable liquids.

ADR PACK GROUP II

TUNNEL RESTRICTION CODE (D/E)

HAZARD No. (ADR) 33

ADR LABEL NO. 3

HAZCHEM CODE •2YE

UN NO. SEA 1219

IMDG CLASS 3

IMDG PACK GR. II

EMS F-E, S-D

ISOPROPANOL CLEANING FLUID

UN NO. AIR 1219
AIR CLASS 3
AIR PACK GR. II

15 REGULATORY INFORMATION

LABELLING



Irritant



Highly Flammable

RISK PHRASES

R11 Highly flammable.
R36 Irritating to eyes.
R67 Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

S16 Keep away from sources of ignition - No smoking.
S25 Avoid contact with eyes.
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S51 Use only in well-ventilated areas.

UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

REVISION DATE NOVEMBER 2010

REV. NO./REPL. SDS 4
GENERATED

SDS NO. 10512

RISK PHRASES IN FULL

R11 Highly flammable.
R36 Irritating to eyes.
R67 Vapours may cause drowsiness and dizziness.

ISOPROPANOL CLEANING FLUID

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.