


Technical Data



AMBERKLENE FG



NSF C1 BIODEGRADABLE CLEANER/DEGREASER



AMBERKLENE FG is a heavy duty, biodegradable industrial cleaner/degreaser. An innovative solvent blend without chlorinated solvents or ozone-depleting components, specially designed for use on food processing and packaging equipment. Authorised for use in inedible product processing, non-processing and exterior areas. The controlled evaporation rate ensures maximum contact time with contamination.

FEATURES

- NSF C1 registered (N°13996) meets USDA 1998 C1 guidelines for use in food industry
- High flash point of 40°C for application safety
- Dissolves grease, oil, lubricants, tar and adhesives
- Penetrates quickly and removes dirt and humidity
- Cleans and degreases equipment, metal parts and machinery
- Neutral product, non-staining
- Does not contain chlorinated solvents
- Does not contain water
- Non-corrosive to metals
- May be harmful to some plastics and will soften some paints
- Fitted with a 360° Spray System for all angle use, even upside down
- Does not contain nut oils or nut oil derivatives



APPLICATIONS

Effective removal of grease, oil, dirt and other contaminants from:

- | | |
|-------------------------------|----------------------------------|
| • Motors | • Mechanical brakes and clutches |
| • Dies | • Pumps |
| • Chains | • Moulds |
| • Generators | • Sprockets |
| • Air tools | • Wire ropes |
| • Material handling equipment | |

DIRECTIONS

- Apply liberally and allow excess to run off, taking care to minimize contamination risk
- Air dry or wipe with absorbent cloth.
- Repeat if necessary.
- Check solvent compatibility for your application prior to use. If in doubt, test on a small area.
- Use with adequate ventilation. Do not use on energised (live) equipment. Allow to dry thoroughly and vent before reactivating system.
- After application, re-lubricate moving parts.
- If parts or equipment are intended to return to a food processing area, rinsing with potable water is required

TECHNICAL DATA

NSF Registered, Category	:	C1
NSF Number	:	137996
Appearance	:	Colourless Liquid
Specific Gravity (@ 20°C)	:	0.78
Flash Point (closed cup)	:	40°C
Boiling Range	:	140 - 170°C
Evaporation Rate (ether = 1)	:	40
Pour Point	:	< -100°C
pH	:	Neutral low
Solubility In Water	:	Low
Kauri-Butanol Value	:	> 200
Packaging	:	500ml Aerosol

STORAGE

The product may be stored at normal ambient temperatures and has a shelf life of not less than 72 months with correct storage. Aerosols should always be stored below 50°C, away from direct heat and naked flame.

HEALTH AND SAFETY

Health and Safety sheet available separately.

MISREPRESENTATION ACT 1967

TRADE DESCRIPTIONS ACT 1968

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

CRC Industries UK Limited, Wylde Road, Bridgwater, Somerset, TA6 4DD

Tel: +44 (0) 1278 727200

Fax: +44 (0) 1278 425644

Web: www.ambersil.com

E-mail: sales.uk@crcind.com