


Blades



493785

Blades	Description	Order Code	Price Each
S60	Heavy duty HSS blade for heavy duty internal deburring in difficult to reach places	137-4069	
S101	Extra fine point HSS blade used for steel and aluminium	137-4080	
S202	Extra fine point HSS blade used for brass and cast iron. For both left and right handed use	137-4081	
S150	HSS blade for 0.75mm radius or larger, holes 1.5mm diameter or larger	137-4098	
BC3200	3.2mm countersink blade. For use with the NB handle and/or SN holder	137-4099	
C12	90 , 12mm countersink for use with the C holder	137-4055	
C20	90 , 20mm countersink for use with the C holder	137-4056	
C30	90 , 30mm countersink for use with the C holder	137-4057	
BC6300	Single flute, 6.3mm countersink. For use with NB handle and/or SN holder	137-4100	
BC8300	Single flute, 8.3mm countersink. For use with NB handle and/or SN holder	137-4101	
BC1040	Single flute, 10.4mm countersink. For use with NB handle and/or SN holder	137-4103	
T80	4mm triangular section x 85mm long Scraper Blade, ground both ends for prolonged life. For use with the Adjustable Scraper Handle only	720-0468	
T120	7mm triangular section x 120mm long Scraper Blade, ground both ends for prolonged life. For use with the Uni Handle only	137-4049	
D50	HSS 3mm Mini Scraper Blade. Most suitable for miniature components	137-4058	
D66	HSS 3.2mm Internal Scraper Blade. Most useful on cross holes	137-4109	
N80	Used in the Double Burr, cutting along the circumference of each face	137-4070	
N80 M42	Used in the Double Burr, cutting along the circumference of each face. The N80 M42 blade is used for stainless steel	137-4105	
N80K M42	Similar to the N80 but ground as shown, to facilitate use in narrow keyways. The N80K M42 Blade is used on stainless steel (2.5mm - 11mm)	137-4106	
N70K	Square Blade for shallow keyways (1.2mm - 8mm)	137-4107	
	Heavy duty blade for wide keyways		

N90K 1.2mm - 6mm

137-4108

Heavy duty blade for wide keyways
N90K (3mm - 15mm)

137-4108