



- A. This Vermason PCB rack is moulded from a carbon black-filled polypropylene compound.
- B. These racks are designed to protect CMOS loaded boards in storage.
- C. Recommended maximum operating temperature is 85°C.
- D. Open carrying handles.
- E. Measurements: 175mm x 500mm.
- F. Weight: 0.7kg.
- G. 20 slots with easy-to-load angle: 3mm x 8mm on a 18.75mm pitch.
- H. Recyclable

"Tools intended for use within the EPA [ESD protected area] shall, as far as is practicable, be so constructed that they do not generate or hold an electrostatic charge ....All tools and machinery, for example electrical, mechanical or pneumatic, shall be so constructed that any non-insulating part of the tool or machine which may touch an ESDS [ESD sensitive items] shall be at EPA ground potential." [EN 61340-5-1 clause 5.2.10 Tools, machinery, dispensers and test equipment]



Properties		UNIT	TEST METHOD
<b>Electrical Properties</b>			
Surface Resistance	<10E6	Ohms/square	ASTM D-257
Volume Resistance	<10E6	Ohms-cm	ASTM D-257
<b>Mechanical Properties</b>			
Tensile Strength @ Break	2860 (19.7)	psi (MPa)	ASTM D-638
Tensile Elongation @ Break	2.5	%	ASTM D-638

ITEM	DESCRIPTION
237215	Conductive PCB Rack, 175mm x 500mm



Made in America

# Vermason

## Conductive PCB Rack, 175mm x 500mm

VERMASON  
 UNIT C, 4TH DIMENSION, FOURTH AVENUE, LETCHWORTH, HERTS, SG6 2TD UK  
 PHONE: +44 (0) 1462-672005, FAX: +44 (0) 1462-670440  
 E-MAIL: [Service@Vermason.co.uk](mailto:Service@Vermason.co.uk), INTERNET: [Vermason.co.uk](http://Vermason.co.uk)

Drawing Number  
**237215**

DATE:  
**February 2009**