




Farnell Code 1956277 - 3m

PINOUT CONFIGURATION

DVI MALE	DVI FEMALE
TMDS DATA 2- 1	1
TMDS DATA 2+ 2	2
TMDS DATA 2/4 SHIELD 3	3
TMDS DATA 2/4 SHIELD 3	3
TMDS DATA 4- 4	4
TMDS DATA 4+ 5	5
DDC CLOCK 6	6
DDC DATA 7	7
TMDS DATA 1- 9	9
TMDS DATA 1+ 10	10
TMDS DATA 1/3 SHIELD 11	11
TMDS DATA 1/3 SHIELD 11	11
TMDS DATA 3- 12	12
TMDS DATA 3+ 13	13
POWER +5V 14	14
GROUND 15	15
HOT PLUG DETECT 16	16
TMDS DATA 0- 17	17
TMDS DATA 0+ 18	18
TMDS DATA 0/5 SHIELD 19	19
TMDS DATA 0/5 SHIELD 19	19
TMDS DATA 5- 20	20
TMDS DATA 5+ 21	21
TMDS CLOCK SHIELD 22	22
TMDS CLOCK+ 23	23
TMDS CLOCK- 24	24
SHELL	SHELL
BRAID	SHELL



NOTE:

1. THIS ITEM CONTAINS PAT. US 6,287,148 B1 RF-BLOK™ SHIELDING DESIGN.
2. WIRE MARKING:
VDC LONDON WWW.VDCTRADING.COM
E193793 9U AWM 20276 80°C 30V VW-1 DVI DUAL LINK DIGITAL

UNIT: mm

CUSTOMER'S APPROVAL: _____ DATE: _____
 FIRST ARTICLE SAMPLE REQUIRED: YES, NO.

ITEM	DESCRIPTION	QTY.	UNIT
1	DVI MALE CONNECTOR (24+1)	1	PCS.
2	BLACK MOLDED PVC HOOD W/VDC LOGO	1	PCS.
3	BLACK #4/40 THUMBSCREW	2	PCS.
4	DVI FEMALE CONNECTOR (24+1)	1	PCS.
5	BLACK MOLDED PVC HOOD W/VDC LOGO	1	PCS.
6	#4/40 HEX-NUT	2	PCS.
7	RF-BLOK™	2	PCS.
8	UL20276 (28AWGx1PAIR+AL-FOIL+DRAIN)x7C +(28AWG WIRE)x5C+AL-FOIL/MY+85% BRAID OVERALL; BLACK PVC JACKET	SEE DWG.	