



## Features:

- Flexible, flame retarded
- General purpose
- Polyolefin tubing



## Specifications:

Shrink ratio : 2:1  
 Shrink temperature : 100°C  
 Minimum operating temperature : -55°C  
 Maximum operating temperature : 135°C

## Specification Values

Property	Test Method	Values
Tensile Strength	ISO 37	10 MPa min.
Ultimate Elongation	ISO 37	250% min.
Specific Gravity	ISO 1183	1.35 max.
Heat Shock	ASTM D2671 (4 hrs at 250°C)	No dripping, cracking or flowing
Heat Ageing Ultimate Elongation	ISO 188 (168 hrs at 175°C) ISO 37	150% min.
Low Temperature Flexibility	ASTM D2671 (4 hrs at -55°C)	No cracking
Flammability (except Clear)	ASTM D876	Pass
Electric Strength	IEC 243	20 KV / mm min.
Corrosion (Copper Contact and Copper Mirror)	ASTM D2671	No corrosion
Water Absorption	ISO 62	0.5% max.
Fluid Resistance Gasoline Hydraulic Fluid Lubricating Oil Tensile Strength Ultimate Elongation	ISO 1817    ISO 37	    7 MPa min. 200% min.
Fungus Resistance Tensile Strength Ultimate Elongation	ISO 846 ISO 37	10 MPa min. 250% min.

## Ordering Data

Ordering Size		Minimum Expanded Diameter		Maximum Recovered Diameter		Nominal Recovered Wall		Standard Reel Length	
Inches	mm	Inches	mm	Inches	mm	Inches	mm	Feet	mm
1/16	1.6	0.063	1.6	0.031	0.8	0.018	0.45	500	150
3/32	2.4	0.093	2.4	0.046	1.2	0.019	0.5	500	150
1/8	3.2	0.125	3.2	0.062	1.6	0.019	0.5	500	150
3/16	4.8	0.187	4.8	0.093	2.4	0.019	0.5	500	150
1/4	6.4	0.25	6.4	0.125	3.2	0.026	0.65	250	75
3/8	9.5	0.375	9.5	0.187	4.8	0.026	0.65	250	75
1/2	12.7	0.5	12.7	0.25	6.4	0.026	0.65	250	75
3/4	19	0.75	19	0.375	9.5	0.029	0.75	200	60
1	25.4	1	25.4	0.5	12.7	0.035	0.9	200	60
1 1/2	38.1	1.5	38.1	0.75	19.1	0.039	1	100	30

**Standard Colours** : Black, Clear, Red, Yellow and Green (other colours available to order)

## Part Number Table

Description	Part Number
Heatshrink, 1.6 mm, Black, 1.2M	SP16/1.2/Black
Heatshrink, 2.4 mm, Black, 1.2M	SP24/1.2/Black
Heatshrink, 3.2 mm, Black, 1.2M	SP32/1.2/Black
Heatshrink, 4.8 mm, Black, 1.2M	SP48/1.2/Black
Heatshrink, 6.4 mm, Black, 1.2M	SP64/1.2/Black
Heatshrink, 9.5 mm, Black, 1.2M	SP95/1.2/Black
Heatshrink, 12.7 mm, Black, 1.2M	SP127/1.2/Black
Heatshrink, 19 mm, Black, 1.2M	SP190/1.2/Black
Heatshrink, 25.4 mm, Black, 1.2M	SP254/1.2/Black
Heatshrink, 38.1 mm, Black, 1.2M	SP381/1.2/Black
Heatshrink, 1.6 mm, Black, 5M	SP16/5/Black
Heatshrink, 2.4 mm, Black, 5M	SP24/5/Black
Heatshrink, 3.2 mm, Black, 5M	SP32/5/Black
Heatshrink, 4.8 mm, Black, 5M	SP48/5/Black
Heatshrink, 6.4 mm, Black, 5M	SP64/5/Black
Heatshrink, 9.5 mm, Black, 5M	SP95/5/Black
Heatshrink, 12.7 mm, Black, 5M	SP127/5/Black

Description	Part Number
Heatshrink, 1.6 mm, Clear, 1.2M	SP16/1.2/Clear
Heatshrink, 2.4 mm, Clear, 1.2M	SP24/1.2/Clear
Heatshrink, 3.2 mm, Clear, 1.2M	SP32/1.2/Clear
Heatshrink, 4.8 mm, Clear, 1.2M	SP48/1.2/Clear
Heatshrink, 6.4 mm, Clear, 1.2M	SP64/1.2/Clear
Heatshrink, 9.5 mm, Clear, 1.2M	SP95/1.2/Clear
Heatshrink, 12.7 mm, Clear, 1.2M	SP127/1.2/Clear
Heatshrink, 19 mm, Clear, 1.2M	SP190/1.2/Clear
Heatshrink, 25.4 mm, Clear, 1.2M	SP254/1.2/Clear
Heatshrink, 38.1 mm, Clear, 1.2M	SP381/1.2/Clear
Heatshrink, 1.6 mm, Clear, 5M	SP16/5/Clear
Heatshrink, 2.4 mm, Clear, 5M	SP24/5/Clear
Heatshrink, 3.2 mm, Clear, 5M	SP32/5/Clear
Heatshrink, 4.8 mm, Clear, 5M	SP48/5/Clear
Heatshrink, 6.4 mm, Clear, 5M	SP64/5/Clear
Heatshrink, 9.5 mm, Clear, 5M	SP95/5/Clear
Heatshrink, 12.7 mm, Clear, 5M	SP127/5/Clear

## Part Number Table

Description	Part Number
Heatshrink, 1.6 mm, Red, 1.2M	SP16/1.2/Red
Heatshrink, 2.4 mm, Red, 1.2M	SP24/1.2/Red
Heatshrink, 3.2 mm, Red, 1.2M	SP32/1.2/Red
Heatshrink, 4.8 mm, Red, 1.2M	SP48/1.2/Red
Heatshrink, 6.4 mm, Red, 1.2M	SP64/1.2/Red
Heatshrink, 9.5 mm, Red, 1.2M	SP95/1.2/Red
Heatshrink, 12.7 mm, Red, 1.2M	SP127/1.2/Red
Heatshrink, 19 mm, Red, 1.2M	SP190/1.2/Red
Heatshrink, 25.4 mm, Red, 1.2M	SP254/1.2/Red
Heatshrink, 38.1 mm, Red, 1.2M	SP381/1.2/Red
Heatshrink, 1.6 mm, Red, 5M	SP16/5/Red
Heatshrink, 2.4 mm, Red, 5M	SP24/5/Red
Heatshrink, 3.2 mm, Red, 5M	SP32/5/Red
Heatshrink, 4.8 mm, Red, 5M	SP48/5/Red
Heatshrink, 6.4 mm, Red, 5M	SP64/5/Red
Heatshrink, 9.5 mm, Red, 5M	SP95/5/Red
Heatshrink, 1.6 mm, Yellow, 1.2M	SP16/1.2/Yellow
Heatshrink, 2.4 mm, Yellow, 1.2M	SP24/1.2/Yellow
Heatshrink, 3.2 mm, Yellow, 1.2M	SP32/1.2/Yellow
Heatshrink, 4.8 mm, Yellow, 1.2M	SP48/1.2/Yellow
Heatshrink, 6.4 mm, Yellow, 1.2M	SP64/1.2/Yellow
Heatshrink, 9.5 mm, Yellow, 1.2M	SP95/1.2/Yellow
Heatshrink, 12.7 mm, Yellow, 1.2M	SP127/1.2/Yellow
Heatshrink, 19 mm, Yellow, 1.2M	SP190/1.2/Yellow
Heatshrink, 25.4 mm, Yellow, 1.2M	SP254/1.2/Yellow
Heatshrink, 38.1 mm, Yellow, 1.2M	SP381/1.2/Yellow
Heatshrink, 1.6 mm, Yellow, 5M	SP16/5/Yellow
Heatshrink, 2.4 mm, Yellow, 5M	SP24/5/Yellow
Heatshrink, 3.2 mm, Yellow, 5M	SP32/5/Yellow
Heatshrink, 4.8 mm, Yellow, 5M	SP48/5/Yellow
Heatshrink, 6.4 mm, Yellow, 5M	SP64/5/Yellow
Heatshrink, 9.5 mm, Yellow, 5M	SP95/5/Yellow
Heatshrink, 12.7 mm, Yellow, 5M	SP127/5/Yellow

Description	Part Number
Heatshrink, 1.6 mm, Green, 1.2M	SP16/1.2/Green
Heatshrink, 2.4 mm, Green, 1.2M	SP24/1.2/Green
Heatshrink, 3.2 mm, Green, 1.2M	SP32/1.2/Green
Heatshrink, 4.8 mm, Green, 1.2M	SP48/1.2/Green
Heatshrink, 6.4 mm, Green, 1.2M	SP64/1.2/Green
Heatshrink, 9.5 mm, Green, 1.2M	SP95/1.2/Green
Heatshrink, 12.7 mm, Green, 1.2M	SP127/1.2/Green
Heatshrink, 19 mm, Green, 1.2M	SP190/1.2/Green
Heatshrink, 25.4 mm, Green, 1.2M	SP254/1.2/Green
Heatshrink, 38.1 mm, Green, 1.2M	SP381/1.2/Green
Heatshrink, 1.6 mm, Green, 5M	SP16/5/Green
Heatshrink, 2.4 mm, Green, 5M	SP24/5/Green
Heatshrink, 3.2 mm, Green, 5M	SP32/5/Green
Heatshrink, 4.8 mm, Green, 5M	SP48/5/Green
Heatshrink, 6.4 mm, Green, 5M	SP64/5/Green
Heatshrink, 9.5 mm, Green, 5M	SP95/5/Green
Heatshrink, 12.7 mm, Green, 5M	SP127/5/Green

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2011.