



- The desk-top ionising blower produces an air flow that is rich in positive and negative ions. Directing the air flow on an object that has a static electricity charge will neutralize the charge.
- The desk-top ionising blower is a portable ionised air blower. It uses a small fan to produce air flow. The volume of air flow is controlled by a variable speed control which provides a wide range of air flow setting. The high voltage AC is applied to a circular arrangement of tungsten steel ion emitter points which results in an intense alternating electric field at the tip of the emitter points. It is this electric field that creates alternating polarity ions in the air flow. To assure that the unit is working properly, the high voltage AC is monitored by an ionisation indicator lamp.
- The desk-top ionising blower features a patented balancing circuit. Also features a patented built-in emitter point clear. Using the point clear takes only seconds. Cleaning the emitter points on a weekly basis prevents the build-up of airborne debris all electrical ionisers are prone to. This keeps your blower working in top form for the life of the unit.
- The desk-top ionising blower was designed for use with sensitive electronic components, where electrostatic discharge is a problem. The desk-top ionising blower can also be used where static electricity causes problems such as : attraction of dirt to product, misalignment of small parts due to electrostatic "jumping" and undesirable adhesion of plastic films due to electrostatic charge.



Product Code:	Description:	Size (mm):	Additional Notes:
1687902	Ionising Blower	190(L) x 110(W) x 245(L)	Each (Ref: 095-0006)

Specification:	Typical Value:
Use Voltage	220V / 50Hz 110V/0Hz
Current Sinking	0.12Amp / 0.25
Air Input	45 - 110CFM
Operating Temperature	32°F (0°C) - 122°F (50°C)
Ozone Quality	0.03PPM (The wind speed transfers to the smallest air blower first 6 inches to measure)
Noise	Is smallest 49dB Biggest 59dB
Engine Case	Aluminium Alloy
Surface	Static Electricity Spraying
Weight	3kg (Net Weight)
Ion Balance (Offset Voltage)	+/- 10V

#### Ion Output (Discharge Time)

Away from Ioniser	Left 300mm	Centre Line	Right 300mm
300mm	-	1.0 sec	-
600mm	3.2 sec	2.5 sec	3.3 sec
900mm	6.4 sec	4.6 sec	6.5 sec

- UK Plug / CE Marked

**Important Notice:** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2011.