



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 9

LOCTITE 3880

sds no. : 168456
V004.1

Revision: 15.06.2011
printing date: 19.10.2011

SECTION 1: Identification of the substance/mixture and of the company/undertaking

Product identifier:

LOCTITE 3880

Relevant identified uses of the substance or mixture and uses advised against:

Intended use:
Epoxy adhesive

Details of the supplier of the safety data sheet:

Henkel Limited
2 Bishop Square Business Park
AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933
Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

Emergency telephone number:

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

Classification of the substance or mixture:

Classification (DPD):

Xi - Irritant

R36/38 Irritating to eyes and skin.

Xi - Irritant

R43 May cause sensitisation by skin contact.

N - Dangerous for the
environment

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Label elements (DPD):

Xi - Irritant



N - Dangerous for the environment



Risk phrases:

R36/38 Irritating to eyes and skin.

R43 May cause sensitisation by skin contact.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases:

S24 Avoid contact with skin.

S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S28 After contact with skin, wash immediately with plenty of water and soap.

S37 Wear suitable gloves.

S61 Avoid release to the environment. Refer to special instructions/Safety data sheets.

Additional labeling:

Contains epoxy constituents. See information supplied by the manufacturer.

Contains:

Bisphenol-A epichlorohydrin resin MW <= 700,

RP Bisphenol F-epichlorohydrin resin, MW<=700,

Phenol-formaldehyde polymer

Other hazards:

None if used properly.

SECTION 3: Composition/information on ingredients

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Silver 7440-22-4	231-131-3	50- 60 %	
Bisphenol-A epichlorhydrin resin MW <= 700 25068-38-6	500-033-5	10- 20 %	Chronic hazards to the aquatic environment 2 H411 Serious eye irritation 2 H319 Skin irritation 2 H315 Skin sensitizer 1 H317
RP Bisphenol F-epichlorohydrin resin, MW<=700 28064-14-4		10- 20 %	
Aliphatic polyepoxide~		1- 10 %	
7,8,9,10,11,12,20,21,22,23,24,25- Dodecahydrodibenzo[i,t][1,4,7,12,15,18]he xaazacyclodocosine-5,13,18,26(6H,19H)- tetrone 68003-28-1	268-115-0	1- 10 %	
Aliphatic Amines, Non Hazardous~		1- 5 %	
Carbinol acetate 112-15-2	203-940-1	1- 5 %	Serious eye irritation 2 H319
Formaldehyde polymer with phenol 9003-35-4		1- 5 %	

Only dangerous ingredients for which a CLP classification is already available are displayed in this table. For full text of the H - statements and other abbreviations see section 16 "Other information". Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Silver 7440-22-4	231-131-3	50 - 60 %	
Bisphenol-A epichlorhydrin resin MW <= 700 25068-38-6	500-033-5	10 - 20 %	N - Dangerous for the environment; R51, R53 R43 Xi - Irritant; R36/38
RP Bisphenol F-epichlorohydrin resin, MW<=700 28064-14-4		10 - 20 %	Xi - Irritant; R36/38, R43 N - Dangerous for the environment; R51/53
Aliphatic polyepoxide~		1 - 10 %	no classification
7,8,9,10,11,12,20,21,22,23,24,25- Dodecahydrodibenzo[i,t][1,4,7,12,15,1 8]hexaazacyclodocosine- 5,13,18,26(6H,19H)-tetrone 68003-28-1	268-115-0	1 - 10 %	no classification
Aliphatic Amines, Non Hazardous~		1 - 5 %	
Carbinol acetate 112-15-2	203-940-1	1 - 5 %	Xi - Irritant; R36
Formaldehyde polymer with phenol 9003-35-4		1 - 5 %	Xi - Irritant; R36/37, R43

SECTION 4: First aid measures**Description of first aid measures:****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

Most important symptoms and effects, both acute and delayed:

SKIN: Rash, Urticaria.

Indication of any immediate medical attention and special treatment needed:

See section: Description of first aid measures

SECTION 5: Firefighting measures

Extinguishing media:

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

Special hazards arising from the substance or mixture:

None
Oxides of carbon, oxides of nitrogen, irritating organic vapors.

Advice for firefighters:

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

SECTION 6: Accidental release measures

Personal precautions, protective equipment and emergency procedures:

Avoid skin and eye contact.

Environmental precautions:

Do not let product enter drains.

Methods and material for containment and cleaning up:

For small spills wipe up with paper towel and place in container for disposal.
For large spills absorb onto inert absorbent material and place in sealed container for disposal.
Wash spillage site thoroughly with soap and water or detergent solution.

Reference to other sections:

See advice in chapter 8

SECTION 7: Handling and storage

Precautions for safe handling:

Use only in well-ventilated areas.
Avoid skin and eye contact.
Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

Hygiene measures:

Good industrial hygiene practices should be observed.

Conditions for safe storage, including any incompatibilities:

Store in sealed original container.

Specific end use(s):
Epoxy adhesive

SECTION 8: Exposure controls/personal protection

Control parameters:

Exposure controls:

Respiratory protection:

Use only in well-ventilated areas.

Hand protection:

The use of chemical resistant gloves such as Nitrile are recommended.

Please note that in practice the working life of chemical resistant gloves may be considerably reduced as a result of many influencing factors (e.g. temperature). Suitable risk assessment should be carried out by the end user. If signs of wear and tear are noticed then the gloves should be replaced.

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties:

Appearance	paste
	silver
Odor	characteristic
pH	No data available / Not applicable
Initial boiling point	> 140 °C (> 284 °F)
Flash point	> 93 °C (> 199.4 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	2,44 g/cm ³
()	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Not available
(Solvent: Water)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable

Oxidising properties

No data available / Not applicable

Other information:

No data available / Not applicable

SECTION 10: Stability and reactivity**Reactivity:**

Strong oxidizing agents.

Chemical stability:

Stable under recommended storage conditions.

Possibility of hazardous reactions:

See section reactivity

Conditions to avoid:

Stable under normal conditions of storage and use.

Protect from direct sunlight.

Incompatible materials:

No data available.

Hazardous decomposition products:

carbon oxides.

SECTION 11: Toxicological information**General toxicological information:**

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

May cause irritation to the digestive tract.

Inhalative toxicity:

May cause irritation to respiratory system.

Skin irritation:

Irritating to the skin.

Eye irritation:

Irritating to eyes.

Sensitizing:

May cause sensitization by skin contact.

Acute toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Silver 7440-22-4	LD50	> 2.000 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Silver 7440-22-4	slightly irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Silver 7440-22-4	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Bisphenol-A epichlorhydrin resin MW <= 700 25068-38-6	positive	bacterial reverse mutation assay (e.g Ames test)	with and without		

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains / surface water / ground water.

Toxic to aquatic organisms

May cause long-term adverse effects in the aquatic environment.

The preparation is classified based on the conventional method outlined in Article 6(1)(a) of Directive 1999/45/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Mobility:

Cured adhesives are immobile.

SECTION 13: Disposal considerations**Waste treatment methods:**

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

SECTION 14: Transport information**Road transport ADR:**

Class:	9
Packaging group:	III
Classification code:	M6
Hazard ident. number:	90
UN no.:	3082
Label:	9
Technical name:	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol A diglycidyl ether,Bisphenol F diglycidyl ether)
Tunnelcode:	(E)

Railroad transport RID:

Class: 9
Packaging group: III
Classification code: M6
Hazard ident. number: 90
UN no.: 3082
Label: 9
Technical name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID,
N.O.S. (Bisphenol A diglycidyl ether,Bisphenol F diglycidyl ether)
Tunnelcode:

Inland water transport ADN:

Class: 9
Packaging group: III
Classification code: M6
Hazard ident. number: 90
UN no.: 3082
Label: 9
Technical name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID,
N.O.S. (Bisphenol A diglycidyl ether,Bisphenol F diglycidyl ether)

Marine transport IMDG:

Class: 9
Packaging group: III
UN no.: 3082
Label: 9
EmS: F-A ,S-F
Seawater pollutant: Marine pollutant
Proper shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID,
N.O.S. (Bisphenol A diglycidyl ether,Bisphenol F diglycidyl ether)

Air transport IATA:

Class: 9
Packaging group: III
Packaging instructions (passenger): 964
Packaging instructions (cargo): 964
UN no.: 3082
Label: 9
Proper shipping name: Environmentally hazardous substance, liquid, n.o.s. (Bisphenol A
diglycidyl ether,Bisphenol F diglycidyl ether)

SECTION 15: Regulatory information**Safety, health and environmental regulations/legislation specific for the substance or mixture:**

VOC content < 3,00 % (As defined in the Council Directive 2004/42/EC)
(1999/13/EC)

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

No classification required.

R36 Irritating to eyes.

R36/37 Irritating to eyes and respiratory system.

R36/38 Irritating to eyes and skin.

R43 May cause sensitisation by skin contact.

R51 Toxic to aquatic organisms.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R53 May cause long-term adverse effects in the aquatic environment.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

This safety data sheet was prepared in accordance with Council Directive 67/548/EEC and its subsequent amendments, and Commission Directive 1999/45/EC.