



## SAFETY DATA SHEET RED GLOSS PAINT

### 1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

**PRODUCT NAME** RED GLOSS PAINT  
**PRODUCT NO.** PRB  
EPRB400  
ZE  
**APPLICATION** Paint  
**SUPPLIER** ELECTROLUBE. A division of  
HK WENTWORTH LTD  
ASHBY PARK, COALFIELD  
WAY,  
ASHBY DE LA ZOUCH,  
LEICESTERSHIRE LE65 1JF  
UNITED KINGDOM  
+44 (0)1530 419600  
+44 (0)1530 416640  
info@hkw.co.uk  
**EMERGENCY TELEPHONE** +44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

### 2 HAZARDS IDENTIFICATION

Extremely flammable  
Repeated exposure may cause skin dryness or cracking.  
Vapours may cause drowsiness and dizziness.  
Irritating to eyes.  
Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.  
**CLASSIFICATION (1999/45)** Xi;R36. F+;R12. R52/53, R66, R67.

#### ENVIRONMENT

Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point. Use appropriate containment to avoid environmental contamination. Avoid release to the environment. Refer to special instructions/safety data sheets. Dispose of waste and residues in accordance with local authority requirements.

#### PHYSICAL AND CHEMICAL HAZARDS

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

### 3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content %	Classification (67/548/EEC)
ACETONE	200-662-2	67-64-1	30-60%	F;R11 Xi;R36 R66 R67
HYDROCARBON DISTILLATE	265-185-4	64742-82-1	10-30%	Xn;R65. N;R51/53. R10,R66.
BUTANE	203-448-7	106-97-8	10-30%	F+;R12
WHITE SPIRIT	265-151-9	64742-49-0	5-10%	Xn;R65. Xi;R38. N;R51/53. R67,R10.
XYLENE	215-535-7	1330-20-7	1-5%	R10 Xn;R20/21 Xi;R38
SOLVENT NAPHTHA (petroleum, light )	265-199-0	64742-95-6	1-5%	Xn;R65. Xi;R37. N;R51/53. R10.

The Full Text for all R-Phrases is Displayed in Section 16

#### COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

## RED GLOSS PAINT

### 4 FIRST-AID MEASURES

**NOTES TO THE PHYSICIAN**

Treat symptomatically

**INHALATION**

Move the exposed person to fresh air at once. Get medical attention.

**INGESTION**

Not relevant.

**SKIN CONTACT**

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

**EYE CONTACT**

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

### 5 FIRE-FIGHTING MEASURES

**EXTINGUISHING MEDIA**

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

**SPECIAL FIRE FIGHTING PROCEDURES**

Move container from fire area if it can be done without risk.

**UNUSUAL FIRE & EXPLOSION HAZARDS**

Aerosol cans may explode in a fire.

### 6 ACCIDENTAL RELEASE MEASURES

**SPILL CLEAN UP METHODS**

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Ventilate well. Absorb in vermiculite, dry sand or earth and place into containers.

### 7 HANDLING AND STORAGE

**USAGE PRECAUTIONS**

Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

**STORAGE PRECAUTIONS**

Store at moderate temperatures in dry, well ventilated area.

### 8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
ACETONE	WEL	500 ppm	1210 mg/m <sup>3</sup>	1500 ppm	3620 mg/m <sup>3</sup>	
BUTANE	WEL	600 ppm	1450 mg/m <sup>3</sup>	750 ppm	1810 mg/m <sup>3</sup>	
HYDROCARBON DISTILLATE	WEL		600 mg/m <sup>3</sup>			
XYLENE	WEL	50 ppm	220 mg/m <sup>3</sup>	100 ppm	441 mg/m <sup>3</sup>	Sk

WEL = Workplace Exposure Limit.  
 Sk = Can be absorbed through skin.

**PROTECTIVE EQUIPMENT**



**RESPIRATORY EQUIPMENT**

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment.

**EYE PROTECTION**

Wear approved, tight fitting safety glasses where splashing is probable.

**OTHER PROTECTION**

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

## RED GLOSS PAINT

### HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. DO NOT SMOKE IN WORK AREA!

### 9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol Liquid
COLOUR	Red
ODOUR	Acetone, ketone.
VOLATILITY DESCRIPTION	Volatile.
SOLUBILITY	Insoluble in water
RELATIVE DENSITY	0.75 @ 20 °C (68 F)
VAPOUR PRESSURE	354.6 kPa
FLASH POINT (°C)	<0 (<32 F) Not noted.
FLAMMABILITY LIMIT - LOWER(%)	0.6
FLAMMABILITY LIMIT - UPPER(%)	13

### 10 STABILITY AND REACTIVITY

#### STABILITY

Stable under normal temperature conditions.

#### CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalis.

### 11 TOXICOLOGICAL INFORMATION

#### INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

#### SKIN CONTACT

Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin. Prolonged or repeated exposure may cause severe irritation.

#### EYE CONTACT

Irritating to eyes.

#### OTHER HEALTH EFFECTS

This substance has no evidence of carcinogenic properties.

#### ROUTE OF ENTRY

Inhalation.

Name	BUTANE
Toxic Conc. - LC 50	658 mg/l/4h (inh-rat)
Name	XYLENE
Toxic Dose 1 - LD 50	4300 mg/kg (oral rat)
Toxic Dose 2 - LD 50	2000 mg/kg (oral-rbt)
Toxic Conc. - LC 50	22.1 mg/l/4h (inh-rat)
Name	ACETONE
Toxic Dose 1 - LD 50	5800 mg/kg (oral rat)
Toxic Dose 2 - LD 50	20,000 mg/kg (oral-rbt)
Toxic Conc. - LC 50	76 ppm/4h (inh-rat)
Name	HYDROCARBON DISTILLATE
Toxic Dose 1 - LD 50	>5000 mg/kg (oral rat)
Toxic Dose 2 - LD 50	>3000 mg/kg (oral-rbt)
Toxic Conc. - LC 50	>11.6 mg/l/4h (inh-rat)
Name	SOLVENT NAPHTHA (petroleum, light )
Toxic Dose 1 - LD 50	>6800 mg/kg (oral rat)
Toxic Dose 2 - LD 50	>3000 mg/kg (oral-rbt)
Toxic Conc. - LC 50	>10.2 mg/l/4h (inh-rat)
Name	WHITE SPIRIT
Toxic Dose 1 - LD 50	>5000 mg/kg (oral rat)

## RED GLOSS PAINT

### 12 ECOLOGICAL INFORMATION

#### ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

Name XYLENE

LC 50, 96 Hrs, Fish mg/l 2.6-8.4

EC 50, 48 Hrs, Daphnia, mg/l 1.0-4.7

Name ACETONE

LC 50, 96 Hrs, Fish mg/l 5540

EC 50, 48 Hrs, Daphnia, mg/l 39

#### Degradability

The product is easily biodegradable.

Name SOLVENT NAPHTHA (petroleum, light )

LC 50, 96 Hrs, Fish mg/l 3.77

EC 50, 48 Hrs, Daphnia, mg/l 7.4

Name WHITE SPIRIT

### 13 DISPOSAL CONSIDERATIONS

#### DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

### 14 TRANSPORT INFORMATION



PROPER SHIPPING NAME	AEROSOLS
ENVIRONMENTALLY HAZARDOUS SUBSTANCE/MARINE POLLUTANT	No.
UN NO. ROAD	1950
ADR CLASS NO.	2
ADR CLASS	Class 2: Gases
ADR PACK GROUP	N/A
TUNNEL RESTRICTION CODE	(D)
ADR LABEL NO.	2.1
UN NO. SEA	1950
IMDG CLASS	2.1
IMDG PACK GR.	N/A
EMS	F-D, S-U
UN NO. AIR	1950
AIR CLASS	2.1
AIR PACK GR.	N/A

### 15 REGULATORY INFORMATION

#### LABELLING



Irritant



Extremely Flammable

## RED GLOSS PAINT

### RISK PHRASES

R12	Extremely flammable.
R36	Irritating to eyes.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

### SAFETY PHRASES

A1	Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children.
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S25	Avoid contact with eyes.
S38	In case of insufficient ventilation, wear suitable respiratory equipment.

### UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

### ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution Act 1974.

### EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

### GUIDANCE NOTES

Workplace Exposure Limits EH40.

## 16 OTHER INFORMATION

### GENERAL INFORMATION

Edit this text

### REVISION COMMENTS

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

### ISSUED BY

Helen O'Reilly

### REVISION DATE

NOVEMBER 2010

### REV. NO./REPL. SDS

4

### GENERATED

### SDS NO.

11023

## RED GLOSS PAINT

### RISK PHRASES IN FULL

R12	Extremely flammable.
R10	Flammable.
R20/21	Harmful by inhalation and in contact with skin.
R65	Harmful: may cause lung damage if swallowed.
R11	Highly flammable.
R36	Irritating to eyes.
R37	Irritating to respiratory system.
R38	Irritating to skin.
R66	Repeated exposure may cause skin dryness or cracking.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.

### DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.